





Rev	AWO #	Description	Date	Appr
-		RELEASED	10/4/04	
A		REDRAWN	02/01/12	
B		UPDATE DRAWING	2/7/20	LH/NL

APPROVED: _____
 DATE: _____ TITLE: _____



RECOMMENDED PCB LAYOUT

SPECIFICATIONS:

- Material: Insulator: PBT, rated UL 94V-0
- Insulator color: Black
- Contacts: Phosphor Bronze
- Plating: Round contact
Gold over Nickel underplate overall
Flat contact
Gold over Nickel underplate on contact area
Matte Tin over Nickel underplate on solder tails
- Electrical: Voltage rating: 150 VAC RMS
Current rating: 1.5 Amp
Contact Resistance: 20 mohms max
Insulation resistance: 1,000 Mohms min @500 VDC
Dielectric withstanding voltage: 1,000 VAC or 1500 VDC RMS @0.5mA For 1 Minute
- Temperature Rating: Operating temperature: -40°C to +85°C
- Environmental: Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM]	
TOLERANCES: EXCEPT AS NOTED	
INCHES	HOLDS
.X ± .10	± .10
.XX ± .020	± .015
.XXX ± .015	± .010
APPROVALS	DATE
DRAWN SS	10/4/04
CHECKED	
APPROVED	

ADAM TECH 909 Rahway Avenue,
 Union, NJ 07083
 Phone: 908-687-5000
 Fax: 908-687-5710

INTERCONNECTS

MODULAR TELEPHONE JACK, 6P6C
 RIGHT ANGLE, PCB

TITLE: _____
 REF: S00008C

SIZE	PART NO.	REV.
X	MTJ-660X1	B
SCALE: NTS	SHEET 1 OF 1	