


APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	3/30/16	
A		UPDATED SPEC.	6/20/16	HR/CK

ADAM P/N	Initial Height
PH-MVS-4355	5.5mm
PH-MVS-4360	6.0mm

Working Stroke	Spring Force
1.0mm	70g


Rated Current	Rated Voltage
3A Max	12V



ADAM P/N	Initial Height
PH-MWS-5365	6.5mm
PH-MWS-5370	7.0mm
PH-MWS-5375	7.5mm
PH-MWS-5380	8.0mm

Working Stroke	Spring Force
1.0mm	70g

Rated Current	Rated Voltage
3A Max	12V



SPECIFICATIONS:

- Material: Plunger: Brass, Gold plated
- Bore: Brass, Gold plated
- Spring: SUS Surface treatment
- Electrical: Contact resistance: 20 mohms max
- Mechanical: Full Stroke: 1.40mm
- Durability: 1,000,000 Cycles
- Temperature Rating: Operating temperature: -55°C to +125°C
- Environmental: Lead free, RoHS compliant.

ADAM TECH

909 Railway Avenue, Union, NJ 07083
 Phone: 908-687-5000 Fax: 908-687-5710

SOLDER CUP SPRING LOADED PIN, STRAIGHT

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE MILLIMETERS TOLERANCES: EXCEPT AS NOTED	
.X MM ± .25	ØXXX ± .013
.XX MM ± .15	
.XXX MM ± .05	
APPROVALS	
DRAWN	HR
CHECKED	CK
APPROVED	
DATE	DATE
3/30/16	3/30/16

SIZE	PART NO.	REV.
X	PH-MVS-XXXX	A
REF: S00770C	SCALE: NTS	SHEET 1 OF 1



6

5

4

3

2

1