


ITEM NO.	PART NUMBER	DESCRIPTION	QTY.	COMPONENT NOTES
1	TLY-13	NEMA 5-15P	1	white overmold
2	30-00245	Wire, 3C, 18 AWG, UL SVT, 300V, 105C, 6.3 mm, VW-1, PVC, white	1	



Wire marking: (UL) E339575 SVT 3X0.824mm²
 (18AWG) 105C 300V VW-1 C(UL) SVT 3X0.824mm²
 (18AWG) 105C 300V VW-1 TENSILITY HLE

Wiring Diagram	
TLY-13	wire color
hot	black
neutral	white
ground	green

Notes:
 Electrical requirements: 10 A at 125 Vac

Revision: A	Date: 12/18/2016	Description: Initial release	Prepared: DN	Notes: RoHS compliant	TENSILITY tel/ 1.541.323.3228 800 877.670.7118 fax 1.541.323.4202 web tensility.com
			Digitally signed by DN Date: 2017.01.26 11:50:36 -08'00' Verified: PS Digitally signed by PS Date: 2017.01.26 16:04:30 -08'00'	Function test: no open, no short circuit, no intermittent Description: Ac cord, 2000 mm, U.S. NEMA 5-15P plug, TLY-13 to tinned, 18 AWG, SVT wire, 30-00245, white	
			Dimensions are in millimeters. Tolerances: X: ± 0.5 mm X.X: ± 0.3 mm X.XX: ± 0.05 mm	Size: Part number: A 11-00028 Scale: 1:2	Sheet 1 of 1