

NIC-mU2-01

MicroUSB 2.0 LAN adapter for mobile devices

- Plug&Play networking via micro USB
- Perfect accessory for your tablet



Features

- Plug&play compact LAN adapter: just plug into a Micro USB port and connect it by a patch cord with your network
- Half/full duplex 10/100Mbps operation
- Supports speed auto-negotiation
- Works with most Windows and Android tablets

Specifications

Interface: Micro USB
Compliant with USB interface v. 1.0/1.1/2.0
Chipset: Realtek 8152B / ASIX AX88772
LAN: RJ-45 LAN connector (10/100 Mbps)
Power consumption: 5 V DC, up to 100 mA
Dimensions: 200 x 22.5 x 16 mm

Packaging

Q'ty in crtn, pcs	100
Crtn volume, CUM	0.046827
Crtn weight, kgs	4.12
Individual package size LxWxH:	50x100x155 mm
Carton size LxWxH:	430x330x330 mm
Country of origin	CN
Barcode	8716309090421
Customs code	8522900090

System requirements

(Mobile) device with LAN connection support
Windows XP/Vista/7/8/10, Android 4+
Free Micro USB port

NOTE: all adapters have identical MAC address, so only single piece can be used per network

Package contents

Micro-USB LAN adapter
Driver CD

Certificates

