

OL13 Series




Detailed introduction:

Material and spec:




Coupling	Threaded Coupling
Shell Material	Nylon66, Fire Resistance: V-0
Insert Material	PPS Max Temperature 260°C
Contact Material	Brass With Gold Plating
Termination	Solder
Cable Outer Diameter Range	I: 4-6.5mm(Default) II: 5-8mm
IP Class	P67/IP68
Mating Cycle	>500
Temperature Range	-25°C~+85°C
Insulation Resistance	2000M Ω

*Provide all black products








Product structure:



Product specifications:



Contact arrangement and spec:

Number of contact	2	3	4	5	6	7	9
Male contact face view							
Rated current(A)	13A	13A	5A	5A	5A	5A	3A
Contact diameter	Φ1.6x2	Φ1.6x3	Φ1x4	Φ1x5	Φ1x6	Φ1x7	Φ0.7x9
Rated voltage(AC.V)	250V	250V	200V	180V	125V	125V	125V
Test voltage(AC.V)1min	1500V	1500V	1500V	1000V	1000V	1000V	1000V

