




Descriptions:	Product Picture:
<p>LED waterproof light, IP67 High lumen output Long life & safe Easy to stall, flexible & sturdy wire Voltage available in DC 5V LED Type: SMD LED, 2.0x2.5mm, 120deg Enamelled copper wire, could be DIY into different shapes</p>	<div style="display: flex; justify-content: space-around;"> <div style="text-align: center;"> <p>LIGHT NO</p>  </div> <div style="text-align: center;"> <p>LIGHT OFF</p>  </div> </div>

Typical Performance (Ta=25°C)

Items	Symbol	Min.	Typ.	Max.	Unit	Product Dimensions:
LED Module Power	Pm	-	3.75	6	w	
Input Voltage(DC)	Vi	-	5	6	V	
Input Current	If	-	0.75	1	A	
Beam Pattern	BP	-	120	-	Deg	
Operating Temperature	Tope	-10 ~ +40			°C	
Storage Temperature	Tsto	-20 ~ +80			°C	

Device Selection Guide

Module No.	Color	Color Temperature (Typ.)	Luminous Flux Per String (Typ.)	LED Qty (Pcs)	Pitch (mm)	Length (mm)	Input Power (DC)
OSWSM51006B-5V	Warm White	3000K	100 lm	100	60	6000	5V
OSWSW51006B-5V	White	20000K	100 lm				

Product Roadmap:

