

FEATURES

- Tubular MCC indicator light
- BA9s base
- 1,000 hr life
- Luminosity of 3.8lm
- Voltage rating of 240V
- Current rating of 13mA
- Length of 28mm
- Diameter of 10mm
- Operation from a DC Supply at Rated Voltage Can Reduce Specified Life by Up to 50%
- Conforms to ANSI/ESD S20.20:2014 and BS EN 61340-5-1:200 on electrostatic discharge

BA9s Indicator Light, Clear, 240 V, 13 mA, 1000h

RS Stock No.: 339-3282



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

Bulbs like this tubular MCC lamp are often used as indicator lights in a number of settings such as automotive and gaming industries. They're also found on instrumentation panels. Offering 1,000 hours of life before it needs to be changed, this indicator light from RS PRO offers 3.8 lm from its clear incandescent bulb. With a voltage rating of 240 V, it has a current rating of 13 mA.

General Specifications

Lamp Base	BA9s
Lamp Size	T3 ¼
Lens Colour	Clear
Luminosity	3.8lm ±20%
Life hours	1000h
Housing Material	Glass
Applications	Automotive industry; Gambling machine industry; Car indicator; Garden lights; Paper lanterns; Battery-powered flashlights

Electrical Specifications

Voltage Rating	240V
Current Rating	13mA
Light Output	3.8lm

Mechanical Specifications

Diameter	10mm
Length	28mm

Operation Environment Specifications

Ambient Operating Temperature

-20°C to 25°C

Approvals

Compliance/Certifications

RoHS, ANSI/ESD S20.20:2014, BS EN 61340-5-1:200

