

## FEATURES

- Tubular MCC indicator light
- BA915d base
- 1,000 hr life
- Luminosity of 45lm
- Voltage rating of 24VAC/DC
- Current rating of 250mA
- Length of 35mm
- Diameter of 16mm
- Conforms to ANSI/ESD S20.20:2014 and BS EN 61340-5-1:200 on electrostatic discharge

# BA15d Indicator Light, Clear, 24 V ac/dc, 250 mA, 1000h

RS Stock No.: 339-33399



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

You'll often find this type of lamp used as an indicator light in the automotive and gaming industries. It has a tubular BA15d format and will provide you with reliable illumination. You'll achieve 1,000 hours of life from the unit that forms part of our trusted RS PRO range. It provides clear and incandescent light and has a luminosity of 45 lm. This light has a voltage rating of 24 V AC/DC and a current rating of 250 mA.

## General Specifications

<b>Lamp Base</b>	BA15d
<b>Lamp Size</b>	T16
<b>Lens Colour</b>	Clear
<b>Luminosity</b>	45lm $\pm$ 20%
<b>Life hours</b>	1000h
<b>Housing Material</b>	Glass
<b>Applications</b>	Automotive industry; Gambling machine industry; Car indicator; Garden lights; Paper lanterns; Battery-powered flashlights

## Electrical Specifications

<b>Voltage Rating</b>	24VAC/DC
<b>Current Rating</b>	250mA
<b>Wattage</b>	6W
<b>Light Output</b>	45lm

## Mechanical Specifications

<b>Diameter</b>	16mm
<b>Length</b>	35mm

## Approvals

### Compliance/Certifications

RoHS, ANSI/ESD S20.20:2014, BS EN 61340-5-1:200



### Dimensions: (mm)




Fig.A