



DCF891H2T-GB

DEWALT 18V XR Brushless 1/2" Hog Ring Anvil Impact Wrench – 2 x 5.0Ah Powerstack

The DCF891 18V XR Impact Wrench with Hog Ring Anvil was designed to easily handle various fastening projects. Get up to 812Nm of fastening torque and 1084Nm of max breakaway torque in a 175mm long body with this compact power tool that offers easy manoeuvrability without sacrificing power. Choose between 4 modes to allow for reliable high-level performance, operability, and versatility. Dark work areas are no problem with this Cordless Impact Wrench, which comes with an LED work light for visibility in dimly lit spaces.

- Tackle wide range of fastening applications with 812Nm of max fastening torque and 1084Nm of max breakaway torque
- Choose the output level based on the job: Control is in your hands with 4 speed settings and a variable speed trigger
- Helps prevent overtightening and fastener run off with Precision Wrench control
- Illuminate dark workplaces using the on-tool LED work light
- Built for comfortable use when working in tight spaces with compact and lightweight design

Standard Equipment

- DCF891 Impact Wrench
- 2 x 5.0Ah Powerstack Batteries (DCP518-XJ)
- Multi-Voltage Charger
- T-Stak Kitbox

BATTERY VOLTAGE	18 V
BATTERY CAPACITY (SUPPLIED)	5.0Ah POWERSTACK
POWER OUTPUT	760W
MAX BREAKAWAY TORQUE	1084Nm
MAX FASTENING TORQUE	812Nm
DRIVE SIZE	1/2" SQUARE DRIVE
NO LOAD SPEED	0-2000 RPM
IMPACTS PER MINUTE	0-3250 IPM
VIBRATION LEVEL	10m/s ²
SOUND LEVEL PRESSURE	91dB
SOUND POWER LEVEL	102dB
WEIGHT	1.7Kg

1 YEAR LIMITED WARRANTY, 3 YEAR LIMITED WARRANTY WHEN REGISTERED

We're confident of the quality of our products and we'll repair, without charge, any defects due to faulty materials or workmanship within the specified warranty.