


# clevis foot LN-50

Part number: 5149

FESTO

For swivel mounting of cylinders DNC, DNGU, DNGUT, DNG, DNU, AEVU, ADVU, ADVUP, ADVUP.



## Data sheet

Feature	Value
Size	50
Based on the standard	ISO 15552 (previously also VDMA 24652, ISO 6431, NF E49 003.1, UNI 10290)
Corrosion resistance classification CRC	2 - Moderate corrosion stress
Ambient temperature	-40 ... 150 °C
Product weight	323 g
Materials note	Free of copper and PTFE Conforms to RoHS
Material mounting	Heat-treatment steel