



Main

Range	Thalassa
Product name	Thalassa TBP
Device application	Multi-purpose
Product or component type	Industrial box
Height	241 mm
Width	194 mm
Depth	107 mm
Internal height	225 mm
Internal width	175 mm
Internal depth	100 mm
Enclosure mounting	Wall mounted
Device composition	1 x body 1 x cover 4 x cover screw
Body type	One piece moulded
Type of front cover	High transparent cover
Cover fixing	Plastic screws
Lock type	Outside sealed area : flat screwdriver captive screw
Removable parts	Cover, by captive screws

Complementary

Material	Polycarbonate
Colour	Grey (RAL 7035) Transparent
Standards	UL 508 A IEC 62208
Product certifications	TÜV UL SEMKO

DEMKO

Electrical insulation class	Class II
IP degree of protection	IP66 conforming to NEMA 4.4X
IK degree of protection	IK08 conforming to IEC 62262
Fire resistance	960 °C
Ambient air temperature for storage	-15...60 °C
Ambient air temperature for operation	-25...80 °C

Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS (date code: YYWW)	Compliant - since 0940 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------