

#### **FEATURES**

- Indicator light
- Wedge groove base
- 10,000 hours life
- Luminosity of 3.53lm
- Voltage rating of 24V
- Current rating of 40mA
- Length of 20mm
- Diameter of 5mm
- Conforms to ANSI/ESD S20.20:2014 and BS EN 61340-5-1:200 on electrostatic discharge

# Wedge Indicator Light, Clear, 24 V, 40 mA, 10000h

RS Stock No.: 655-9801



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



#### **Product Description**

If you're looking for a lamp to provide illumination in an automotive or gambling context or for an instrumentation panel, consider this wedge indicator light from the trusted RS PRO range. With a luminosity of 3.53 lumens, it's efficient and long-lasting (10,000 hours of life before needing to be replaced). The voltage rating is 24 V and the current rating is 40 mA.

#### **General Specifications**

Lamp Base	Wedge
Lamp Size	T1 ½
Lens Colour	Clear
Luminosity	3.53lm±20%
Life hours	10,000h
Filament Type	Vacuum Type
Housing Material	Glass
Applications	Automotive industry; Gambling machine industry; Car indicator; Garden lights; Paper lanterns; Battery-powered flashlights

#### **Electrical Specifications**

Voltage Rating	24V
Current Rating	40mA+10%
Light Output	3.53lm

#### **Mechanical Specifications**

Diameter	5.0mm
Length	20.0mm



### **Approvals**

Compliance/Certifications

RoHS, ANSI/ESD S20.20:2014, BS EN 61340-5-1:200



## **Incandescent Light Bulbs**



