


0604 KSS Nylon Cable Gland



- Material: UL approved Nylon 66, 94V-2.
- Color: Black, available in other colors.



Unit: mm

	Item No.	Thread	Moubling Hole D1	D2	B1	L1	L2	L3	For Cable	Packing
	AG-12	M12xP1.25	12.0	8.3	6.9	7.90	19.6	13.6	3 ~ 6.5	50 pcs / Bag
	AG-12L	M12xP1.5	12.0	8.3	6.9	7.90	19.6	13.6	3 ~ 6.5	
	AG-16	M16xP1.5	16.0	10.9	10.5	15.50	23.4	16.9	5 ~ 10	
	AG-16S	M16xP1.5	16.0	10.9	10.5	10.00	23.4	16.9	5 ~ 10	
	AG-20	M20xP1.5	20.0	15.0	14.0	15.00	28.5	18.5	10 ~ 14	
	AG-20S	M20xP1.5	20.0	15.0	14.0	10.00	28.5	18.5	10 ~ 14	
	AG-25	M25xP1.5	25.0	18.6	18.4	15.20	29.4	22.3	13 ~ 18	
	AG-25S	M25xP1.5	25.0	18.6	18.4	10.00	29.4	22.3	13 ~ 18	
	AG-32	M32xP1.5	32.0	26.0	25.0	14.70	34.5	25.7	18 ~ 25	25 pcs / Bag
	AG-40	M40xP1.5	40.0	33.7	33.0	18.40	41.7	31.3	22 ~ 32	10 pcs / Bag
	AG-50	M50xP1.5	50.0	41.9	40.0	17.80	44.2	31.3	30 ~ 38	
	AG-63	M61xP1.5	61.0	55.0	44.0	18.50	44.6	32.7	34 ~ 44	
	AG-63M	M63xP1.5	63.0	54.9	44.0	18.50	44.6	32.7	34 ~ 44	
	AG-63L	M63xP1.5	63.0	56.6	51.5	25.40	49.0	36.8	42 ~ 50	
※	AG-16F	PF 1/2"	20.8	11.0	10.0	9.50	20.7	18.7	5 ~ 10	50 pcs / Bag
※	AG-20F	PF 1/2"	20.8	14.6	13.0	9.30	24.1	18.5	6 ~ 13	
	AGJ-14	PF 1/4"	14.0	8.2	6.5	8.00	19.6	13.2	3 ~ 6.5	50 pcs / Bag
	AGJ-17	PF 3/8"	17.0	10.8	10.3	14.70	23.5	16.8	5 ~ 10	
	AGJ-21	PF 1/2"	21.0	14.9	14.0	12.90	28.3	18.4	10 ~ 14	
	AGJ-27	PF 3/4"	27.0	18.5	18.0	14.70	29.1	22.3	13 ~ 18	
	AGJ-34	PF 1"	34.0	26.0	25.0	14.84	34.5	25.7	18 ~ 25	25 pcs / Bag
※ NEW	AG-12D	M12xP1.25	12.0	7.3	6.5	8.00	19.7	12.7	3 ~ 6.5	50 pcs / Bag
※ NEW	AG-16D	M16xP1.5	16.0	10.7	10.1	8.00	23.3	16.1	5 ~ 10	
※ NEW	AG-20D	M20xP1.5	20.0	14.1	12.4	10.00	25.0	18.1	8 ~ 12	
※ NEW	AG-25D	M25xP1.5	25.0	18.0	17.1	8.00	30.0	20.0	11 ~ 17	
※ NEW	AG-32D	M32xP1.5	32.0	25.7	21.2	10.00	35.4	24.1	15 ~ 21	25 pcs / Bag
※ NEW	AG-40D	M40xP1.5	40.0	32.7	28.2	10.00	39.4	27.5	20 ~ 28	10 pcs / Bag
※ NEW	AG-50D	M50xP1.5	50.0	42.2	35.3	12.00	43.4	31.6	27 ~ 35	
※ NEW	AG-63D	M63xP1.5	63.0	55.0	42.4	12.00	46.4	33.7	32 ~ 42	