

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [50695-8000](#)
Status: **Active**
Description: 4.00mm Pitch Crimp Terminal, Female, for 51154 Housing, Reel

Documents:

[Drawing \(PDF\)](#) [Packaging Specification SPK-50695-001 \(PDF\)](#)
[Product Specification PS-501598-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-51154-001 \(PDF\)](#)

General

Product Family	Crimp Terminals
Series	50695
Application	Power
Crimp Quality Equipment	Yes
Product Name	OBD-II
UPC	800753368538


Physical

Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	180.000/mg
Packaging Type	Reel
Plating min - Mating	0.889µm
Plating min - Termination	0.914µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.30-2.30mm
Wire Size AWG	N/A
Wire Size mm ²	AVS 0.5, AVS 0.5F, AVS 0.75F, AVS 0.85, AVSS 0.5, AVSS 0.5F, AVSS 0.75F, AVSS 0.85, CAVS 0.5, CAVS 0.85, CAVUS 0.5, CAVUS 0.85

Material Info

Reference - Drawing Numbers

Packaging Specification	SPK-50695-001
Product Specification	PS-501598-001, PS-51154-001, RPS-51154-002
Sales Drawing	SD-50695-001



EU RoHS

ELV and RoHS Compliant
REACH SVHC Contains SVHC: No
Low-Halogen Status Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

50695Series

Use With

51154 4.00mm Pitch Crimp Terminal, Female

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Japan

Description	Product #
Applicator for M211A	0573673000
Bench Press	