


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION  
 © COPYRIGHT ALL INTERNATIONAL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
J	—	P	LTR	DESCRIPTION	DATE	DWN	APVD
		D6		REVISED PER ECR-19-017851	26NOV19	SM	DZ
		E			17DEC20	MG	DZ



1. APPLICABLE CONTACT PART NUMBER;  
 TAB CONTACT: 175150-□ (#20-#16AWG)  
 175149-□ (#26-#22AWG)  
 2 TO BE USED WITH THE CONTACT WHICH IS RATED 105°C MAX  
 3 MATERIAL: PA66, UL94 V-0, GWIT 775°C

1-176271-5	130°C MAX	3	GREEN 绿	2	1-176282-5
1-176271-1	130°C MAX	3	NATURAL 自然色		1-176282-1 2
176271-□	105°C MAX	PA66	BLACK 黒	2	176282-9
			BLUE 青		176282-6
			YELLOW 黄		176282-4
			RED 赤		176282-2
	NATURAL 自然色			176282-1	
MATING CONN. PART NUMBER 嵌合相手型番	TEMPERATURE RATING 定格温度	TYPE 種類	HOUSING COLOR 色	Pos. 極数	PART NUMBER 型番

1. 適用端子型番;  
 リセコンタクト: 175150-□ (#20-#16AWG)  
 175149-□ (#26-#22AWG)  
 2 適用コンタクトの使用温度は最大105°C

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: $\leq 10$ $\pm 0.2$ $10 < \leq 30$ $\pm 0.25$ $30 <$ $\pm 0.3$	DWN Y.NARISAWA 19NOV1990	<b>TE</b> TE Connectivity
	ANGLES FINISH $\pm 3^\circ$	CHK Y.FUJITA 19NOV1990	
MATERIAL SEE TABLE		APVD N.ONOUE 20NOV1990	NAME AMP UNIVERSAL POWER CONN. 3.96mm PITCH CAP HOUSING 2 Pos. (SGL ROW) AMP ユニバーサルパワーコネクタ 2極 3.96mmピッチ キャップハウジング
		PRODUCT SPEC 108-5302	SIZE CAGE CODE DRAWING NO RESTRICTED TO
		APPLICATION SPEC 114-5142	A3 00779 C-176282
		WEIGHT	RESTRICTED CUSTOMER SCALE NTS SHEET 1 OF 1 REV E

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-176282-1](#)