MALLORY Mallory Sonalert Products Inc.	Part #	PT-2736FPQ
Sales Outline Drawing	Revision	E

May not be suitable for all medical and aerospace applications. Specifications: Contact Mallory Sonalert to discuss your application.

	<u> </u>		
Resonant Frequency (Hz)	3500 ± 500		
Operating Voltage (Vp-p)	3 ~ 28		
Rated Voltage (Vp-p)	12		
Current Consumption (mA/max)	8.0 at Rated Voltage		
Sound Pressure Level (dB/min)	90 at 30cm at Rated voltage		
Operating Temperature (°C)	-20 ~ +70		
Storage Temperature (°C)	-30 ~ +80		
Housing	ABS 757 UL94HB plastic resin		
	(Color: Black)		
Lead Pins	Tin Plated Brass $M = Main$		
	(Ceramic); F = Feedback; G = Ground		
	(Metal)		
Weight (Grams)	2.8		
Condition by wave soldering (°C)	$245 \pm 5 / 3 \pm 0.5 \text{ sec}$		
Condition by hand soldering (°C)	350 ± 20 / within 5 sec		
Options	For other options contact factory		

NO CIRCUITRY

Dimensions: (units: mm) ROHS Compliant

