


SPECIFICATIONS
 Current Rating: 5A AC,DC
 Voltage Rating: 250V AC,DC
 Temperature Range: -25°C ~ +85°C
 Contact Resistance: 10mΩ Max
 Insulation Resistance: 1000MΩ Min
 Withstanding Voltage: 1500V AC/minute
 Pin Material: Brass/Tin-plated
 Material: PBT30%GF,UL94V-0
 Color: Natural(Black)

Ordering Information & Dimensions

| PART NO. | Dimensions | | PART NO. | Dimensions | |
|----------|------------|-------|----------|------------|-------|
| | A | B | | A | B |
| 01 | --- | 6.65 | 07 | 18.00 | 24.65 |
| 02 | 3.00 | 9.65 | 08 | 21.00 | 27.65 |
| 03 | 6.00 | 12.65 | 09 | 24.00 | 30.65 |
| 04 | 9.00 | 15.65 | 10 | 27.00 | 33.65 |
| 05 | 12.00 | 18.65 | 11 | 30.00 | 36.65 |
| 06 | 15.00 | 21.65 | 12 | 33.00 | 39.65 |

| | | | | | | | |
|------|--------------|------------|------|--------------------|-------------|---------|--------|
| | | | | Ninigi | | TITLE: | |
| | | | | UNIT | SCALE | SHEET | 1 of 2 |
| | | | | mm | 1 : 1 | 1 of 2 | |
| | | | | DRAWN BY | APPROVED BY | | |
| | | | | 董正一 | 董正一 | | |
| | | | | 2001.02.01 | 2001.02.01 | | |
| | | | | GENERAL TOLERANCE | | | |
| | | | | X, X±0.25 | ANGLE± | | |
| | | | | X, XX±0.15 | | | |
| | | | | X, XXX±0.05 | | | |
| B2 | EN1409020004 | 2014.09.02 | 郭木忠 | | | | |
| REV. | DESCRIPTION | DATE | NAME | | | | |
| | | | | DRAW NO. : MFGK-xx | | REV. B2 | |



| | | | | | | | |
|------|--------------|------------|------|-------------------------------|----------------------------------|--------|---|
| | | | | Ninigi | | | |
| | | | | UNIT | SCALE | SHEET | TITLE: |
| | | | | mm | 1 : 1 | 2 of 2 | 3.00mm PITCH 90° WAFER, MICRO-FIT |
| | | | | DRAWN BY 董正一 2001.02.01 | APPROVED BY 董正一 2001.02.01 | | |
| | | | | GENERAL TOLERANCE | | | DRAW NO. : MFGK-xx |
| | | | | X, X±0.25 | ANGLE± | | |
| B2 | EN1409020004 | 2014.09.02 | 郭木忠 | X, XX±0.15 | | | REV. B2 |
| REV. | DESCRIPTION | DATE | NAME | X, XXX±0.05 | | | |