



Replacement element part numbers

Elements with Nitrile seals						
Model	18P-1	18P-2	28P-1	28P-2	38P-1	38P-2
02C	G04242	G04250	G04258	G04266	G04274	G04282
05C	G04243	G04251	G04259	G04267	G04275	G04283
10C	G04244	G04252	G04260	G04268	G04276	G04284
20C	G04245	G04253	G04261	G04269	G04277	G04285
02QH	G04290	G04298	G04306	G04314	G04322	G04330
05QH	G04291	G04299	G04307	G04315	G04323	G04331
10QH	G04292	G04300	G04308	G04316	G04324	G04332
20QH	G04293	G04301	G04309	G04317	G04325	G04333

Elements with Fluoroelastomer seals						
Model	18P-1	18P-2	28P-1	28P-2	38P-1	38P-2
02C	G04236	G04254	G04262	G04270	G04278	G04286
05C	G04237	G04255	G04263	G04271	G04279	G04287
10C	G04238	G04256	G04264	G04272	G04280	G04288
20C	G04239	G04257	G04265	G04273	G04281	G04289
02QH	G04294	G04202	G04310	G04318	G04326	G04334
05QH	G04295	G04203	G04311	G04319	G04327	G04335
10QH	G04296	G04304	G04312	G04320	G04328	G04336
20QH	G04297	G04305	G04313	G04321	G04329	G04337

Ordering Information

Standard products table

Part number	Supersedes	Flow (l/min)	Model number	Element length	Media rating (µ)	Seals	Indicator	Bypass settings	Ports	Replacement elements
18P110QBT1MG121	18P-1-10C-TW6-98-B2B2-1	80	18P	Length 1	10	Nitrile	Electrical	7.0 bar	GW*	G04244
18P110QBM3MG121	18P-1-10C-M2-98-B2B2-1	80	18P	Length 1	10	Nitrile	Visual	7.0 bar	GY*	G04244
18P120QBT1MG121	18P-1-20C-TW6-98-B2B2-1	100	18P	Length 1	20	Nitrile	Electrical	7.0 bar	GW*	G04245
18P120QBM3MG121	18P-1-20C-M2-98-B2B2-1	100	18P	Length 1	20	Nitrile	Visual	7.0 bar	GY*	G04245
18P210QBT1MG121	18P-2-10C-TW6-98-B2B2-1	130	18P	Length 2	10	Nitrile	Electrical	7.0 bar	GW*	G04252
18P210QBM3MG121	18P-2-10C-M2-98-B2B2-1	130	18P	Length 2	10	Nitrile	Visual	7.0 bar	GW*	G04252
18P220QBT1MG121	18P-2-20C-TW6-98-B2B2-1	150	18P	Length 2	20	Nitrile	Electrical	7.0 bar	GY*	G04253
18P220QBM3MG121	18P-2-20C-M2-98-B2B2-1	150	18P	Length 2	20	Nitrile	Visual	7.0 bar	GY*	G04253
28P110QBT1MG161	28P-1-10C-TW6-98-C2C2-1	120	28P	Length 1	10	Nitrile	Electrical	7.0 bar	G1*	G04260
28P110QBM3MG161	28P-1-10C-M2-98-C2C2-1	120	28P	Length 1	10	Nitrile	Visual	7.0 bar	G1*	G04260
28P120QBT1MG161	28P-1-20C-TW6-98-C2C2-1	150	28P	Length 1	20	Nitrile	Electrical	7.0 bar	G1*	G04261
28P120QBM3MG161	28P-1-20C-M2-98-C2C2-1	150	28P	Length 1	20	Nitrile	Visual	7.0 bar	G1*	G04261
28P210QBT1MG161	28P-2-10C-TW6-98-C2C2-1	250	28P	Length 2	10	Nitrile	Electrical	7.0 bar	G1*	G04268
28P210QBM3MG161	28P-2-10C-M2-98-C2C2-1	250	28P	Length 2	10	Nitrile	Visual	7.0 bar	G1*	G04268
38P110QBT1MG201	38P-1-10C-TW6-98-D2D2-1	340	38P	Length 1	10	Nitrile	Electrical	7.0 bar	G1½*	G04276
38P110QBM3MG201	38P-1-10C-M2-98-D2D2-1	340	38P	Length 1	10	Nitrile	Visual	7.0 bar	G1½*	G04276
38P120QBT1MG201	38P-1-20C-TW6-98-D2D2-1	420	38P	Length 1	20	Nitrile	Electrical	7.0 bar	G1½*	G04277
38P120QBM3MG201	38P-1-20C-M2-98-D2D2-1	420	38P	Length 1	20	Nitrile	Visual	7.0 bar	G1½*	G04277
38P210QBT1MG201	38P-2-10C-TW6-98-D2D2-1	560	38P	Length 2	10	Nitrile	Electrical	7.0 bar	G1½*	G04284
38P210QBM3MG201	38P-2-10C-M2-98-D2D2-1	560	38P	Length 2	10	Nitrile	Visual	7.0 bar	G1½*	G04284
38P220QBT1MG201	38P-2-20C-TW6-98-D2D2-1	700	38P	Length 2	20	Nitrile	Electrical	7.0 bar	G1½*	G04285
38P220QBM3MG201	38P-2-20C-M2-98-D2D2-1	700	38P	Length 2	20	Nitrile	Visual	7.0 bar	G1½*	G04285

Note: Filter assemblies ordered from the product configurator on the next page are on extended lead times. Where possible, please make your selection from the table above.

Part numbers shown are for steel. Other material options available. Go to www.parker.com for details. Dimensions and pressures are for reference only and are subject to change.