# C7 Draw Latch

18.3

(.72)

Concealed

Keeper

Latch

164

(6.45)

Latched

151

(5.95)

45.7

(1.80)

Latch

5.2±0.1

(.204±.003)

12.7±0.1

Unlatched

Assembly

15.1

(.60)

26.2

(1.03)

Keeper

76.2±6.4

 $(3.00 \pm .25)$ 

12.7±0.1

29.5 (1.16)

**Bracket** 





- Low profile design
  - Cushions impact and accommodates misalignment

**Non-corrosive materials** 

# **Material and Finish**

Latch:

2.4

(.09)

1.6

(.06)

Thermoplastic elastomer black Link and bushings: Glass reinforced nylon

Keeper and bracket: Stainless steel

## **Performance Details**

Small:

Clamping force: 49 N (11 lbf)

Large:

Clamping force: 176 N (40 lbf) Flammability rating: UL94-HB


### **Installation Notes**


Small:


Install assembly with four Ø 4 (.170) rivets or M4 (No. 8) screws (not supplied)

Large:

Install assembly with four Ø5 (.204) rivets or M5 (No. 10) screws (not supplied)







Size	Keeper Style	Assembly Part Number
Small	Concealed	C7-10
	Reverse Keeper	C7-11
	Right Angle Keeper	C7-12
Large	Concealed	C7-20



See table

Assembly complete with keeper



