



### Main

Range	Thalassa
Product name	Thalassa TBP
Device application	Multi-purpose
Product or component type	Industrial box
Height	138 mm
Width	93 mm
Depth	72 mm
Internal height	125 mm
Internal width	80 mm
Internal depth	65 mm
Enclosure mounting	Wall mounted
Device composition	1 x body 1 x cover 4 x cover screw
Quantity per set	Set of 2
Body type	One piece moulded
Type of front cover	Low plain cover
Cover fixing	Plastic screws
Lock type	Outside sealed area : flat screwdriver captive screw
Removable parts	Cover, by captive screws

### Complementary

Material	Polycarbonate
Colour	Grey ( RAL 7035 )
Standards	IEC 62208 UL 508 A
Product certifications	SEMKO UL TÜV

## DEMKO

Electrical insulation class	Class II
IP degree of protection	IP66 conforming to NEMA 4.4X
IK degree of protection	IK08 conforming to IEC 62262
Fire resistance	960 °C
Ambient air temperature for storage	-15...60 °C
Ambient air temperature for operation	-25...80 °C

### Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS (date code: YYWW)	Compliant - since 0940 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product end of life instructions	Need no specific recycling operations

### Contractual warranty

Warranty period	18 months
-----------------	-----------