

Features

- High quality “gold” masking tape, for extremely sharp edges
- Precise & intricate masking
- Excellent adhesion on all surfaces, also on plastic and rubber
- Professional painting – tape provides a fine boundary line
- U.V. protected for masking in direct sunlight
- The tape sticks, stays and removes cleanly
- Indoor and outdoor use

Applications

Modeling, Airbrushing, Arts, Craft, Hobby, Smaller DIY tasks

Recommendations for Use

Temperature: between +15°C and +30°C. Surface must be clean and free from dust and grease. Pressure sensitive adhesive must be applied with a maximum of pressure in order to achieve maximum pressure level. The indicated level of performance will be reached after a bonding period of 24 hours at +23°C

Storage and Shelf Life

Clean and dry in a well ventilated area, preferably at a temperature between +10°C and +30°C. Stored under these conditions shelf life will be a minimum of 24 months

Specification

Thickness	0.09 mm
Adhesive Strength	5 Ncm
Tensile Strength	75 N / 25 mm
Temperature Resistance	100 °C
Short Term Temperature	150°C (for 20 Minutes)
Elongation	5%
Adhesive Material	Acrylic
Tape Backing Material	Paper

Product Range



RND 605-00247



RND 605-00248



RND 605-00249



RND 605-00250



RND 605-00251



RND 605-00252

Type Nr.	Length	Width	Quantity
RND 605-00247	18 m	1 mm	Pair
RND 605-00248	18 m	2 mm	Pair
RND 605-00249	18 m	3 mm	Pair
RND 605-00250	18 m	6 mm	Pair
RND 605-00251	18 m	10 mm	Pair
RND 605-00252	18 m	18 mm	Piece