


# FTP Cat5e Patch cord, grey, 0.25 m

PP22-0.25M

- Perfect connection
- Foil shielded for a reliable connection
- Gold plated contacts



## Features

- Foil shielded patch cord, 8P8C
- 50u" gold plated contacts
- Molded strain reliefs

## Specifications

Category: Enhanced category 5  
 Type: FTP ( foil shielded)  
 Frequency bandwidth: Max. 100 MHz  
 Compliance with ANSI / TIA / EIA-568B standards  
 Conductor: AWG 26 (7 x 0.15 mm wire), CCA  
 Conductor insulation: HDPE 0.85 mm  
 Shielding: AL foil  
 LDPE filler: n/a  
 Polyester tape: yes  
 Drain wire: yes (7 x 0.12 mm CCA)  
 Jacket material: PVC  
 Jacket braiding: n/a  
 Jacket outer diameter: 5.0 mm  
 Length: conform item description  
 Color: conform item description

## Packaging

Q'ty in crtn, pcs	300
Crtn volume, CUM	0.022
Crtn weight, kgs	7.82
Individual package size LxWxH:	170x120x10 mm
Carton size LxWxH:	385x310x185 mm
Country of origin	CN
Barcode	8716309074773
Customs code	8544421000

## Certificates

