


ESPE

LOW VOLTAGE DC CABLE



Specification:

Model	DC.CAB.2400.0150.E
DC Socket	5,5x2,5mm
Recommended voltage	0 - 48V
Max Current	5A
Dielectric Strength	500 VDC
Operating temperature	-20°C to +70°C
Cord Length	1463 mm
Cable Diameter	2x2mm
Wire Diameter	2x0,5mm ²
ROHS	+



Made in PRC