

[Find by Feature](#)
[Browse by Category](#)
[Share](#)

Enter part number or keyword

[Search Results \(243\)](#)
[Search Options](#)

243 Results:

1 2 3 4

12048074 Female Metri-Pack 150 Tin Plated Terminal, Cable range 0.50 - 1.00 mm2

[12048074 FL2G 1,0 S Version III](#)

[12048074 FLRY-B 0,75 to 1,0 S VERSION I](#)

[12048074 FLRY-B 0,75 to 1,0 S Version II](#)

[13838337 ASM CONN 3 F M/P 150 SLD](#)

[12045809 CONN 10 F M/P 150 BLK SLD](#)

[12092884 CONN 5 F M/P 150 CRM SLD](#)

[12129123 CONN 5 F M/P 150 280 SLD](#)

[12059471 CONN 7 F M/P 150 480 SLD](#)

[12092799 CONN 4 F M/P 150 280 SLD](#)

1 2 3 4

Keyword: 12048074

Female Metri-Pack 150 Tin Plated Terminal, Cable range 0.50 - 1.00 mm2

Part #12048074

[Attributes](#)
[Documents \(10\)](#)
[Related Products \(1\)](#)

Part #:	12048074
Description:	Female Metri-Pack 150 Tin Plated Terminal, Cable range 0.50 - 1.00 mm2
Product Type:	Terminal
Status:	Active
Blade size [mm]:	1.5
Terminal family:	Metri-Pack
Series:	150
Gender:	Female
Sealed:	Sealed
Plating:	Tin
Minimum Cable Core Cross Section [mm2]:	0.50
Maximum Cable Core Cross Section [mm2]:	1.00
Minimum Cable Diameter [mm]:	2.03
Maximum Cable Diameter [mm]:	2.80
Current range [A]:	14
Temperature range []:	-40 to 125

Certain products listed on this website may be subject to restricted usage or distribution or may not be available. For additional information, please contact your local sales office.