



DIN7A SERIES

75 Ω DIN 1.0/2.3 JACKS & PLUGS

Mates with:

RFB8T, RFA6T, RFB6T, RF179, GRF7H-C

SPECIFICATIONS

For complete specifications see www.samtec.com?DIN7A-TH, www.samtec.com?DIN7A-BH or www.samtec.com?DIN7A-CA

Shell Material:


Brass
Contact:
Copper Alloy
Insulator Material:


Operating Temp Range: -65 °C to +125 °C

Impedance: 75Ω

Working Voltage: 250 Vrms

Dielectric Withstanding:





Due to technical progress, all designs, specifications and components are subject to change without notice.