

Features

- Adjustment is via a graduated knob, which can be locked with a grub screw
- Incorporates a mechanical stop providing over-pressure protection for spring and micro switch
- DIN 43650 connector

RS PRO G 1/4 Pressure Switch, 10 bar

RS Stock No.:

363-5968



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

- RS Pro pressure switch features 10 bar maximum operating pressure and G 1/4 connection. This pressure switch allows micro switch operation once a pre-set pressure is reached. It can be adjusted via a graduated knob, which can be locked with a grub screw. The pressure switch meets DIN 43650 standards.*

General Specifications

Connection Thread Size	1/4
Connection Thread Standard	G
Connection	G 1/4
Contact Operation	Normally Closed, Normally Open
LED Indicator	No
Maximum Operating Pressure	10 bar
Maximum Operating Temperature	+80°C
Maximum Pressure Setting	25 bar
Minimum Operating Pressure	1 bar
Minimum Operating Temperature	-20°C
Minimum Pressure Setting	0 bar
Output Range	1 to 10 bar
Output Type	NO/NC
Pressure Setting Range	0 to 25 bar
Pressure Type	Positive Pressure
Type	Adjustable
Frequency Rating	120 cpm
Material	Steel

Electrical Specifications

Voltage Rating	250 V ac/dc
----------------	-------------

Protection Category

IP Rating	IP65
-----------	------