



3666 - PLUG-IN REDUCER



maximum working pressure	30 bar 3 MPa 435 psi
working temperature	-25 to 150 °C -13 to 302 °F 248 to 423 °K
vacuum capability	755 mm Hg
body	FDA CHEMICAL NICKEL PLATED BRASS
'O'-rings	FKM
collar	FDA CHEMICAL NICKEL PLATED BRASS
sealing washer	FDA CHEMICAL NICKEL PLATED BRASS

Part Nb	ØD1 (MM)	ØD2 (MM)	ØG (mm)	L (mm)	L1 (mm)	L2 (mm)	(kg)
	All ▼	All ▼	All ▼	All ▼	All ▼	All ▼	All ▼
3666 04 06	4	6	10	35	19.5	18	.008
3666 04 08	4	8	10	35.5	20	18	.009
3666 06 08	6	8	12	38	20	20.5	.012
3666 06 10	6	10	12	43.5	25	21	.015
3666 08 10	8	10	15	44	25	21.5	.016
3666 08 12	8	12	15	44	26	20.5	.018
3666 10 12	10	12	17.5	50	26	27	.026
3666 12 14	12	14	19.5	53	28	28.5	.032