



ENGLISH

Datasheet

RS Pro Portable Hydraulic Filtration Unit, 25 to 100L/min, 24V dc

RS Stock No: **862-5622**



Product Details

RS Pro portable hydraulic filtration unit has maximum flow rate of 25 to 100 L/min. It has a BSP thread standard and voltage rating of 24 V dc. The low maintenance, running and commissioning costs of this system compared with other oil coolers makes them cost-effective and practical solution. It is suitable for building into many applications including hydraulic lifts, mobile cranes, railway machinery and construction machinery, injection moulding equipment, machine tools and agricultural machinery.

Features and Benefits

- BSP thread standard
- Operating pressure of 16 bar (dynamic), 25 bar (static)
- Flow rate: 25 to 100 L/min



ENGLISH

Specifications:

Depth	167 mm
Dimensions	322.5 x 277 x 167 mm
Height	322.5 mm
Maximum Flow Rate	25 to 100 L/min
Maximum Operating Pressure	16 (Dynamic), 25 (Static) bar
Thread Size	1 in
Thread Standard	BSP
Voltage	24 V dc
Weight	6 kg
Width	277 mm
Air Flow	600 m ³ /h
Current Rating	2.9 A
IP Rating	IP64
Noise Level	75 dB(A)
Power Rating	70 W