

MILAN S.r.l. a socio unico

**Head Office – Export department:**  
 Viale Europa, 74  
 20090 Cusago (MI) Italy  
 T. +39 02 9039.4556-4158  
 F. +39 02 9039.4551  
 www.taskercables.com

**Ufficio Commerciale e Centro Distribuzione**  
 Viale Europa 72 Strada F12  
 20090 Cusago (MI) Italy  
 T. +39 02 9039.0037-0059  
 F. +39 02 9039.0049  
 www.tasker.it

## Technical Datasheet ✓RoHS<sub>3</sub>

### tasker® C101 2x0,50 mm<sup>2</sup>

### Flat Divisible Audio Divisible Cable



**CATEGORY** Flat Cable (See Audio Catalogue)  
**APPLICATIONS** Speaker and Home Theatre installation

- A:** Red and Black Soft **PVC** Sheath.  
 Outer cable dimension 2,00x4,10 (±0,20) mm.
- B:** Both conductors in O.F.C. Red Copper.  
 Formation with 0,20 mm wires.  
 Nominal cross section 2x0,50 mm<sup>2</sup>.

**MARKING** Cable not Marked  
**CUSTOM PRODUCTION** This product may be custom produced also in **L.S.Z.H.** polymer, **PE** or **PUR**.

#### Cable Properties

<b>Conductor Resistance</b>	38 Ω/Km
<b>Max Rated Voltage</b>	49 V
<b>Operative Temperature</b>	-15/+70°C

<b>USE</b>	<b>X</b>	Indoor	Interno Edificio	<b>INSTALLATION</b>	<b>X</b>	Fixed	Fissa	<b>INFORMATION</b>	<b>X</b>	RoHS3 Compliant
<b>Impiego</b>		Outdoor Limited	Esterno Limitato	<b>Posa</b>	<b>X</b>	Restricted Mobile	Mobile Limitata	<b>Informazioni</b>	<b>X</b>	Ver. B / 16.05.19
		Outdoor	Esterno			Mobile	Mobile			
		Outdoor Direct Burial	Esterno Interrato			Mobile in Drag Chain	Mobile in Catena			