

## A50.20.063 0...200°C L1=40x9mm copper alloy CL.2

### Bimetallic thermometer TYP48-50

Item number: 12579999

Quantity: 1 pcs.

Order code: A50.20.063-H-C1L-040DMFRGD-1ZZZZZZZQI-ZZZ

2BZTM5003

Overview: A50.20.063 0...200°C L1=40x9mm copper alloy CL.2  
Case material: steel, zinc plated  
Pointer: aluminium, black Window: flat instrument glass detachable, with retainer screw; Mat.=Cu-alloy G1/2B  
Dial background: white  
\*WIKA\*  
Data sheet: TM50.03

Details: Bimetallic thermometer TYP48-50  
Model: A50 Standard version  
Design: standard, steel case  
Nominal size [NG, d1]: 63 mm  
Case material: steel, zinc plated  
Unit: °C  
Scale range: 0 °C ... 200 °C  
Insertion length L1: 40 mm  
Stem diameter: 9 mm  
Stem material: copper alloy  
Thermowell: detachable, with retainer screw;  
Thermowell material: Cu-alloy  
Process connection: G 1/2 B  
Manufacturer logo: \*WIKA\*  
Pointer: aluminium, black  
Window: flat instrument glass  
Accuracy class: class 2 per EN 13190  
Dial background: White  
Data sheet: TM50.03