

WP-GR HF CTA M40 BK - Corrugated tube screw connection



3241223

<https://www.phoenixcontact.com/us/products/3241223>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Corrugated pipe adapter, with internal thread, for connecting corrugated pipes to HEAVYCON EVO M40 plastic cable glands or ADVANCE M40 plastic housings, straight, black, IP66.

Commercial data

Item number	3241223
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BF68
Product key	BF7DSA
Catalog page	Page 585 (C-4-2013)
GTIN	4046356860857
Weight per piece (including packing)	41.38 g
Weight per piece (excluding packing)	41.38 g
Customs tariff number	39269097
Country of origin	DE

WP-GR HF CTA M40 BK - Corrugated tube screw connection



3241223

<https://www.phoenixcontact.com/us/products/3241223>

Technical data

Product properties

Product type	Corrugated pipe screw connection
Application	Cable gland
Type	Internal thread
Thread type	metric

Material specifications

Material	PA
Flammability rating according to UL 94	V2
Material for screw connection	PA
Components	free from silicone, halogen, and cadmium

Cable/line

Halogen-free	yes
--------------	-----

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP66
Ambient temperature (operation)	-40 °C ... 115 °C

Mounting

Assembly instructions	The corrugated pipe adapter is used in the screw connection instead of the union nut. Thanks to the adapter, corrugated pipes can be used.
-----------------------	--

WP-GR HF CTA M40 BK - Corrugated tube screw connection



3241223

<https://www.phoenixcontact.com/us/products/3241223>

Classifications

ECLASS

ECLASS-11.0	27430311
ECLASS-13.0	27430311
ECLASS-12.0	27430311

ETIM

ETIM 9.0	EC001178
----------	----------

UNSPSC

UNSPSC 21.0	39121300
-------------	----------

WP-GR HF CTA M40 BK - Corrugated tube screw connection



3241223

<https://www.phoenixcontact.com/us/products/3241223>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

WP-GR HF CTA M40 BK - Corrugated tube screw connection



3241223

<https://www.phoenixcontact.com/us/products/3241223>

Accessories

WP-PA HF-SL 42,5 BK - Protective hose

3240848

<https://www.phoenixcontact.com/us/products/3240848>



Protective hose, material: PA, UV-resistant: yes, flexible, degree of protection: IP40, color: black, flammability rating in acc. with UL 94: HB, inner diameter: 36 mm, Total length: 10 m

WP-PA HF 42,5 BK - Protective hose

3241089

<https://www.phoenixcontact.com/us/products/3241089>



Protective hose, material: PA 6, UV-resistant: yes, flexible, degree of protection: IP68, color: black, flammability rating in acc. with UL 94: V0, inner diameter: 36 mm, Total length: 25 m

WP-GR HF CTA M40 BK - Corrugated tube screw connection



3241223

<https://www.phoenixcontact.com/us/products/3241223>

WP-PA HF-HB 42,5 BK - Protective hose

3240844

<https://www.phoenixcontact.com/us/products/3240844>



Protective hose, material: PA 6, UV-resistant: yes, flexible, degree of protection: IP68, color: black, flammability rating in acc. with UL 94: HB, inner diameter: 36 mm, Total length: 25 m

Phoenix Contact 2024 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com