

82H - Short metric keys




Standards:

NF ISO 2936, ISO 2936, DIN ISO 2936, ASME B18.3.2M

Description:

- Manufactured in silicon steel.
- Finish: phosphate-coated.



	A [mm]	Length L [mm]	Height H [mm]	Weight [g]
82H.0.9	0.9	38.0	12.0	0.3
82H.1.3	1.3	45.0	13.0	0.7
82H.1.5	1.5	38.0	13.0	5.0
82H.10	10.0	112.0	40.0	100.0
82H.11	11.0	118.0	42.0	130.0
82H.12	12.0	125.0	45.0	165.0
82H.13	13.0	135.0	50.0	205.0
82H.14	14.0	140.0	55.0	260.0
82H.15	15.0	150.0	58.0	310.0
82H.16	16.0	154.0	60.0	370.0
82H.17	17.0	160.0	63.0	440.0
82H.18	18.0	170.0	66.0	540.0
82H.19	19.0	180.0	70.0	640.0
82H.2	2.0	50.0	16.0	2.0
82H.2.5	2.5	62.0	17.0	3.0
82H.22	22.0	200.0	80.0	950.0
82H.23	23.0	210.0	85.0	1100.0
82H.24	24.0	224.0	90.0	1300.0
82H.27	27.0	250.0	100.0	1300.0
82H.3	3.0	65.0	20.0	5.0
82H.3.5	3.5	66.0	22.0	8.0
82H.32	32.0	315.0	125.0	1400.0
82H.4	4.0	70.0	25.0	10.0
82H.4.5	4.5	75.0	26.0	15.0
82H.5	5.0	80.0	28.0	20.0
82H.6	6.0	90.0	32.0	30.0
82H.7	7.0	95.0	34.0	45.0
82H.8	8.0	100.0	36.0	60.0

82H.9

9.0

105.0

38.0

80.0