




**SPECIFICATION
CONTROL DRAWING
Crystal Resonator**

FREQUENCY
25.000000MHz



Holder Style	2x16x05 4-pad
Mode	Fundamental
Adjustment Tolerance	± 30PPM at 25°C
Temperature Stability	± 50 PPM
Operating Temp. Range	-20°C to +70°C
Load Capacitance	10 pF
ESR	100 Max Ohm
Static Capacitance (C0)	Unspecified pF
Ageing	+/-3PPM 1st Year
Marking	AEL 25 WWYY

Amdt Date	Change Note	AEL Code
		X25M000000S187
		Issue Ref A