

## Han A Hood Coupler Thermoplastic 1 Lever



Image is for illustration purposes only. Please refer to product description.

|                    |   |
|--------------------|---|
| Part number        | 19 20 003 0727  |
| Specification      | Han A Hood Coupler Thermoplastic 1 Lever  |
| HARTING eCatalogue | <a href="https://b2b.harting.com/19200030727">https://b2b.harting.com/19200030727</a> |

### Identification

|                          |                        |
|--------------------------|------------------------|
| Category                 | Hoods/Housings         |
| Series of hoods/housings | Han A <sup>®</sup>     |
| Type of hood/housing     | Cable to cable housing |

### Version

|                      |   |
|----------------------|---|
| Locking type         | Single locking lever                                |
| Size                 | 3 A   |
| Version              | Top entry   |
| Cable entry          | 1x M20  |
| Field of application | Standard Hoods/housings for industrial applications |

### Technical characteristics

|  |  |
|--|--|
| Limiting temperature                   | -40 ... +125 °C                                    |
| Degree of protection acc. to IEC 60529 | IP44<br>IP65 / IP67 with seal screw 09 20 000 9918 |
| Type rating acc. to UL 50 / UL 50E     | 4<br>4X<br>12                                      |

### Material properties

|   |                      |
|---|----------------------|
| Material (hood/housing)                   | Polycarbonate (PC)   |
| Colour (hood/housing)                     | RAL 9005 (jet black) |
| Material flammability class acc. to UL 94 | V-0                  |
| RoHS                                      | compliant            |



Pushing Performance

## Material properties

|                             |           |
|-----------------------------|-----------|
| ELV status                  | compliant |
| China RoHS                  | e         |
| REACH Annex XVII substances | No        |
| REACH ANNEX XIV substances  | No        |
| REACH SVHC substances       | No        |

## Specifications and approvals

|           |        |
|-----------|--------|
| Approvals | DNV GL |
| CE        | Yes    |

## Commercial data

|                                |  |
|--------------------------------|--|
| Packaging size                 | 10                                       |
| Net weight                     | 16.3 g                                   |
| Country of origin              | Romania                                  |
| European customs tariff number | 85389099                                 |
| eCl@ss                         | 27440202 Shell for industrial connectors |