

FEATURES AND SPECIFICATIONS

Features and Benefits

- Sizes 2 to 15 circuits
- Housing lance provides extra terminal retention
- Friction locks provide secure mating

Reference Information

Packaging: Bag
 UL File No.: E29179
 CSA File No.: LR19980
 Use With: 50079/50058
 Mates With: 53398, 53261, 53047, 53048 and 51047
 Designed In: Millimeters

Electrical


Voltage: 125V
 Current: 1.0A
 32 AWG—0.8A
 Contact Resistance: 20mΩ max.
 Dielectric Withstanding Voltage: 250V AC/1 min.
 Insulation Resistance: 100 MΩ min.

Physical


Housing: PBTP, UL 94V-0
 Temperature: -40 to +85°C

molex® 1.25mm (.049") Pitch Wire-to-Wire and Wire-to-Board Receptacle

51021



Micro Connectors



ORDERING INFORMATION AND DIMENSIONS

Circuits	Order No.	Dimension	
		A	B
2	51021-0200	4.25 (.167)	1.25 (.049)
3	51021-0300	5.50 (.217)	2.50 (.098)
4	51021-0400	6.75 (.266)	3.75 (.148)
5	51021-0500	8.00 (.315)	5.00 (.197)
6	51021-0600	9.25 (.364)	6.25 (.246)
7	51021-0700	10.50 (.413)	7.50 (.295)
8	51021-0800	11.75 (.463)	8.75 (.344)
9	51021-0900	13.00 (.512)	10.00 (.393)
10	51021-1000	14.25 (.561)	11.25 (.441)
11	51021-1100	15.50 (.610)	12.50 (.492)
12	51021-1200	16.75 (.659)	13.75 (.541)
13	51021-1300	18.00 (.709)	15.00 (.590)
14	51021-1400	19.25 (.758)	16.25 (.639)
15	51021-1500	20.50 (.807)	17.50 (.688)