




SPECIFICATION CONTROL DRAWING Crystal Resonator

FREQUENCY
48.000000MHz



Holder Style Mode Adjustment Tolerance Temperature Stability Operating Temp. Range Load Capacitance ESR Static Capacitance (C0) Marking	1,6 x 1,2mm 4P Fundamental ± 20 PPM at 25°C ± 10 PPM -30°C to +85°C 10 pF 45 Max Ohm Unspecified pF 48.00 / YYWW
---	--

Amdt Date	Change Note	AEL Code		
20 NOV 15	-30 DegC min, CL now 10pF	X48M000000S020		
		<table border="1" style="width: 100%; border-collapse: collapse;"> <tr> <th style="width: 70%;">Issue Ref</th> <td style="text-align: center;">A</td> </tr> </table>	Issue Ref	A
Issue Ref	A			