



ENGLISH

Datasheet

## RS Pro Portable Hydraulic Filtration Unit, 25 to 150L/min, 24V dc

RS Stock No: **862-5635**



### Product Details

RS Pro portable hydraulic filtration unit has maximum flow rate of 25 to 150 L/min. It has a BSP thread standard and voltage rating of 24 V dc. The low maintenance, running and commissioning costs of this system compared with other oil coolers makes them cost-effective and practical solution. It is suitable for building into many applications including hydraulic lifts, mobile cranes, railway machinery and construction machinery, injection moulding equipment, machine tools and agricultural machinery.

### Features and Benefits

- BSP thread standard
- Operating pressure of 16 bar (dynamic), 25 bar (static)
- Flow rate: 25 to 100 L/min



ENGLISH

### Specifications:

Depth	167 mm
Dimensions	322.5 x 277 x 167 mm
Height	322.5 mm
Maximum Flow Rate	25 to 150 L/min
Maximum Operating Pressure	16 (Dynamic), 25 (Static) bar
Thread Size	1 in
Thread Standard	BSP
Voltage	24 V dc
Weight	6 kg
Width	277 mm
Air Flow	600 m <sup>3</sup> /h
Current Rating	2.9 A
IP Rating	IP64
Noise Level	75 dB(A)
Power Rating	70 W