


FEATURES

- Low Cost
- Wide Range of Band Width
-

APPLICATIONS

- Telecommunications



© TGS CRYSTALS LTD.

SPECIFICATION FOR 450KHZ *


Characteristics Part Number	Centre Frequency (KHz)	Insertion Loss (dB Max.)	Passband Ripple (dB Max.)	6dB Bandwidth (KHz)Min	50dB Bandwidth (KHz)Max	Stop band Att ±100KHz (dB)Min	Input/output Impedance (Ω)
CFA450BW	fo±2.0	4	2	±15.0	±30.0	40	1500
CFA450CW	±	4	2	±12.5	±24.0	40	1500
CFA450DW	±	4	2	±10.0	±20.0	40	1500
CFA450EW	±	6	2	±7.5	±15.0	40	1500
CFA450FW	±	4	2	±6.0	±12.5	40	2000
CFA450GW	±	6	2	±4.5	±10.0	40	2000
CFA450HW	±	6	2	±3.0	±9.0	40	2000
CFA450IW	±	6	2	±2.0	±7.5	40	2000
CFA450HTW	±	6	2	±3.0	±9.0	60	2000
CFA450ITW	±	6	2	±2.0	±7.5	60	2000

SPECIFICATION FOR 455KHZ *


Characteristics Part Number	Centre Frequency (KHz)	Insertion Loss (dB Max.)	Passband Ripple (dB Max.)	6dB Bandwidth (KHz)Min	50dB Bandwidth (KHz)Max	Stop band Att ±100KHz (dB)Min	Input/output Impedance (Ω)
CFA455BW	fo±2.0	4	2	±15.0	±30.0	40	1500
CFA455CW	±	4	2	±12.5	±24.0	40	1500
CFA455DW	±	4	2	±10.0	±20.0	40	1500
CFA455EW	±	6	2	±7.5	±15.0	40	1500
CFA455FW	±	4	2	±6.0	±12.5	40	2000
CFA455GW	±	6	2	±4.5	±10.0	40	2000
CFA455HW	±	6	2	±3.0	±9.0	40	2000
CFA455IW	±	6	2	±2.0	±7.5	40	2000
CFA455HTW	±	6	2	±3.0	±9.0	60	2000
CFA455ITW	±	6	2	±2.0	±7.5	60	2000

* Specifications Subject to Change Without Notice


DIMENSIONS



TEST CIRCUIT



FREQUENCY CHARACTERISTICS



PACKAGE

- Standard package in bulk: 1000 pcs/ box, 10 box/carton

PART NUMBER GUIDE

TGS	CF	A	455	E	W
Mark	Ceramic Filter	A: Height-8.0mm	Centre Freq.	Grade	W: 5 Pin

e.g. Full P/N.: TGS CFA 455 E W