




### Heatsinks for SMD




art. no.	↳ [mm]	R <sub>th</sub> [K/W]
ICK SMD C 7 ...	7	33
ICK SMD C 10 ...	10	26
ICK SMD C 17 ...	17	17



art. no.	↳ [mm]	R <sub>th</sub> [K/W]
ICK SMD E 15 ...	15.3	27
ICK SMD E 22 ...	22.3	21
ICK SMD E 29 ...	29.0	18



art. no.	↳ [mm]	R <sub>th</sub> [K/W]
ICK SMD F 8 ...	8	74
ICK SMD F 10 ...	10	71
ICK SMD F 17 ...	17	42
ICK SMD F 19 ...	19	37
ICK SMD F 21 ...	21	33
ICK SMD F 26 ...	26	26



art. no.	↳ [mm]	R <sub>th</sub> [K/W]
ICK SMD G 8 ...	8	73
ICK SMD G 10 ...	10	70
ICK SMD G 13 ...	13	61
ICK SMD G 17 ...	17	41
ICK SMD G 19 ...	19	36
ICK SMD G 21 ...	21	32

please indicate: ... surface treatment  
 SA=black anodised  
 MI=solderable surface