Thin Film Precision Chip Resistors **Multicomp**

RoHS


Compliant



Features

- Advanced thin film technology
- Very tight tolerance 0.1%
- Low TCR
- Miniature size 0201

Construction




1	Alumina Substrate
2	Bottom Electrode
3	Top Electrode
4	Edge Electrode
5	Barrier Layer
6	External Electrode
7	Resistor Layer
8	Overcoat
9	Marking

Dimensions

Resistor Case Inch (mm)	L	w	т	D1	D2
0201 (0603)	0.58 ±0.05	0.29 ±0.05	0.23 ±0.05	0.12 ±0.05	0.15 ±0.05

Derating Curve



Standard Electrical Specifications

Size	Power Rating @ 70°C	Operating Temperature	Max. Operating Voltage	Max. Overload Voltage	Tolerance	Resistance Range	TCR (PPM/°C)			
0201	1/22 \\/	55°C - 1155°C	15)/	201/	0.1%	49.9Ω - 4.99kΩ	±25			
0201	0201 1/32 W 55°C ~ ·	1/32 W 55°C ~ +155°C		$1/32 \text{ W}$ $55^{\circ}\text{C} \sim +155^{\circ}\text{C}$ 15V		1/32 W 55°C ~ +155°C 15V 30V	300	0.1%	49.9Ω - 33kΩ	±50

Operating Voltage = $\sqrt{(P * R)}$ or Max. Operating voltage listed above, whichever is lower. Overload Voltage = 2.5 * $\sqrt{(P * R)}$ or Max. Operating voltage listed above, whichever is lower.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro




Dimensions : Millimetres

ltem	Tolerance >0.1%	Test Method
Temperature Coefficient Resistor (TCR)	As per Spec.	MIL-STD-202 Method 304 +25/-55/+25/+125/+25°C
Short Time Overload	ΔR±0.2%	JIS-C-5201-1 4.13 RCWV*2.5 or Max. overload voltage whichever is lower for 5 seconds
Insulation Resistance	>9999 MΩ	MIL-STD-202 Method 302 Apply 100Vbc for 1 minute
Endurance	$\begin{array}{c} \Delta R{\pm}0.2\% \\ {>}7k\Omega \rightarrow \Delta R{\pm}0.5\% \\ {\leq}7k\Omega \rightarrow \Delta R{\pm}0.2\% \end{array}$	MIL-STD-202 Method 108A 70±2°C, RCWV for 1000hrs with 1.5hrs "ON" and 0.5hrs "OFF"
Damp Heat with Load	ΔR±0.3%	MIL-STD-202 Method 103B 40±2°C, 90 ~ 95% R.H. RCWV for 1000hrs with 1.5hrs "ON" and 0.5hrs "OFF"
Bending Strength	ΔR±0.1%	JIS-C-5201-1 4.33 Bending amplitude 3 mm for 10 seconds
Solderability	95% min. coverage	MIL-STD-202 Method 208H 245±5°C for 3 seconds
Resistance to Soldering Heat	ΔR±0.1%	MIL-STD-202 Method 210E 260±5°C for 10 seconds
Dielectric Withstand Voltage	-	MIL-STD-202 Method 301 Max. overload voltage for 1 minute
Low Temperature Operation	ΔR±0.2%	JIS-C-5201-1 4.36 1 hour, -65°C, followed by 45 minutes of RCWV
High Temperature Exposure	ΔR±0.5%	MIL-STD-202 Method 108 at +155°C for 1000hrs


Environmental Characteristics

*RCWV(Rated continuous working voltage)= $\sqrt{(P^*R)}$ or Max. Operating voltage whichever is lower Storage Temperature: 15~28°C; Humidity: < 80%RH

Soldering Condition



IR Reflow Soldering




Wave Soldering (Flow Soldering)

- (1) Time of IR reflow soldering at maximum temperature point 260°C = 10s
- (2) Time of wave soldering at maximum temperature point 260°C = 10s
- (3) Time of soldering iron at maximum temperature point 410°C = 5s



Packaging


Packing Quantity & Reel Specifications



ØA	ØB	ØC	w	т	Paper Tape (EA)
178 ±1	60 +1	13.5 ±0.7	9.5 ±1	11.5 ±1	10,000

Dimensions : Millimetres


Paper Tape Specifications



Α	В	W	E	F	P٥	P 1	P 2	ΦD₀	Т
0.4 ±0.05	0.7 ±0.05	8 ±0.1	1.75 ±0.05	3.5 ±0.05	4 ±0.1	2 ±0.05	2 ±0.05	1.55 ±0.03	0.42 ±0.02
								D : .	

Dimensions : Millimetres

Recommend Land Pattern



Α	В	С
0.25mm	0.3mm	0.4mm ±0.2mm



multicomp PRO

Part Number Table

Description	Part Number	Description	Part Number
Resistor, Thin Film, 60R4, 0.1%, ±25ppm, 1/32W, 0201	MC003005	Resistor, Thin Film, 475R, 0.1%, ±25ppm, 1/32W, 0201	MC003644
Resistor, Thin Film, 178R, 0.1%, ±25ppm, 1/32W, 0201	MC003056	Resistor, Thin Film, 3K65, 0.1%, ±25ppm, 1/32W, 0201	MC003743
Resistor, Thin Film, 475R, 0.1%, ±25ppm, 1/32W, 0201	MC003106	Resistor, Thin Film, 3K74, 0.1%, ±25ppm, 1/32W, 0201	MC003744
Resistor, Thin Film, 300R, 0.1%, ±25ppm, 1/32W, 0201	MC003081	Resistor, Thin Film, 4K02, 0.1%, ±50ppm, 1/32W, 0201	MC003972
Resistor, Thin Film, 665R, 0.1%, ±25ppm, 1/32W, 0201	MC003123	Resistor, Thin Film, 1K2, 0.1%, ±25ppm, 1/32W, 0201	MC003151
Resistor, Thin Film, 187R, 0.1%, ±25ppm, 1/32W, 0201	MC003597	Resistor, Thin Film, 2K61, 0.1%, ±25ppm, 1/32W, 0201	MC003725
Resistor, Thin Film, 301R, 0.1%, ±25ppm, 1/32W, 0201	MC003082	Resistor, Thin Film, 274R, 0.1%, ±50ppm, 1/32W, 0201	MC003839
Resistor, Thin Film, 390R, 0.1%, ±25ppm, 1/32W, 0201	MC003095	Resistor, Thin Film, 390R, 0.1%, ±50ppm, 1/32W, 0201	MC003857
Resistor, Thin Film, 4K87, 0.1%, ±25ppm, 1/32W, 0201	MC003220	Resistor, Thin Film, 280R, 0.1%, ±50ppm, 1/32W, 0201	MC003840
Resistor, Thin Film, 174R, 0.1%, ±25ppm, 1/32W, 0201	MC003055	Resistor, Thin Film, 549R, 0.1%, ±50ppm, 1/32W, 0201	MC003875
Resistor, Thin Film, 470R, 0.1%, ±25ppm, 1/32W, 0201	MC003105	Resistor, Thin Film, 71R5, 0.1%, ±25ppm, 1/32W, 0201	MC003014
Resistor, Thin Film, 3K48, 0.1%, ±25ppm, 1/32W, 0201	MC003202	Resistor, Thin Film, 2K67, 0.1%, ±25ppm, 1/32W, 0201	MC003726
Resistor, Thin Film, 1K05, 0.1%, ±50ppm, 1/32W, 0201	MC003369	Resistor, Thin Film, 560R, 0.1%, ±50ppm, 1/32W, 0201	MC003876
Resistor, Thin Film, 1K47, 0.1%, ±50ppm, 1/32W, 0201	MC003384	Resistor, Thin Film, 3K92, 0.1%, ±50ppm, 1/32W, 0201	MC003971
Resistor, Thin Film, 7K32, 0.1%, ±50ppm, 1/32W, 0201	MC003465	Resistor, Thin Film, 1K78, 0.1%, ±25ppm, 1/32W, 0201	MC003169
Resistor, Thin Film, 680R, 0.1%, ±25ppm, 1/32W, 0201	MC003124	Resistor, Thin Film, 2K43, 0.1%, ±25ppm, 1/32W, 0201	MC003184
Resistor, Thin Film, 3K65, 0.1%, ±25ppm, 1/32W, 0201	MC003205	Resistor, Thin Film, 2K67, 0.1%, ±50ppm, 1/32W, 0201	MC003412
Resistor, Thin Film, 69R8, 0.1%, ±50ppm, 1/32W, 0201	MC003237	Resistor, Thin Film, 5K6, 0.1%, ±50ppm, 1/32W, 0201	MC003989
Resistor, Thin Film, 392R, 0.1%, ±25ppm, 1/32W, 0201	MC003096	Resistor, Thin Film, 825R, 0.1%, ±25ppm, 1/32W, 0201	MC003134
Resistor, Thin Film, 10K7, 0.1%, ±50ppm, 1/32W, 0201	MC003483	Resistor, Thin Film, 130R, 0.1%, ±50ppm, 1/32W, 0201	MC003266
Resistor, Thin Film, 178R, 0.1%, ±25ppm, 1/32W, 0201	MC003594	Resistor, Thin Film, 113R, 0.1%, ±25ppm, 1/32W, 0201	MC003035
Resistor, Thin Film, 84R5, 0.1%, ±25ppm, 1/32W, 0201	MC003022	Resistor, Thin Film, 115R, 0.1%, ±25ppm, 1/32W, 0201	MC003036
Resistor, Thin Film, 3K4, 0.1%, ±25ppm, 1/32W, 0201	MC003201	Resistor, Thin Film, 255R, 0.1%, ±50ppm, 1/32W, 0201	MC003297
Resistor, Thin Film, 71R5, 0.1%, ±50ppm, 1/32W, 0201	MC003238	Resistor, Thin Film, 95R3, 0.1%, ±50ppm, 1/32W, 0201	MC003252
Resistor, Thin Film, 4K75, 0.1%, ±25ppm, 1/32W, 0201	MC003219	Resistor, Thin Film, 102R, 0.1%, ±50ppm, 1/32W, 0201	MC003255
Resistor, Thin Film, 976R, 0.1%, ±50ppm, 1/32W, 0201	MC003366	Resistor, Thin Film, 15K, 0.1%, ±50ppm, 1/32W, 0201	MC003498
Resistor, Thin Film, 21K5, 0.1%, ±50ppm, 1/32W, 0201	MC003515	Resistor, Thin Film, 1K62, 0.1%, ±25ppm, 1/32W, 0201	MC003165
Resistor, Thin Film, 14K7, 0.1%, ±50ppm, 1/32W, 0201	MC003497	Resistor, Thin Film, 82R, 0.1%, ±25ppm, 1/32W, 0201	MC003558
Resistor, Thin Film, 255R, 0.1%, ±25ppm, 1/32W, 0201	MC003611	Resistor, Thin Film, 887R, 0.1%, ±25ppm, 1/32W, 0201	MC003675
Resistor, Thin Film, 261R, 0.1%, ±25ppm, 1/32W, 0201	MC003612	Resistor, Thin Film, 187R, 0.1%, ±50ppm, 1/32W, 0201	MC003283
Resistor, Thin Film, 510R, 0.1%, ±50ppm, 1/32W, 0201	MC003333	Resistor, Thin Film, 261R, 0.1%, ±50ppm, 1/32W, 0201	MC003298
Resistor, Thin Film, 732R, 0.1%, ±50ppm, 1/32W, 0201	MC003352	Resistor, Thin Film, 1K91, 0.1%, ±50ppm, 1/32W, 0201	MC003397
Resistor, Thin Film, 7K5, 0.1%, ±50ppm, 1/32W, 0201	MC003466	Resistor, Thin Film, 26K7, 0.1%, ±50ppm, 1/32W, 0201	MC003526
Resistor, Thin Film, 511R, 0.1%, ±50ppm, 1/32W, 0201	MC003334	Resistor, Thin Film, 619R, 0.1%, ±25ppm, 1/32W, 0201	MC003657
Resistor, Thin Film, 715R, 0.1%, ±50ppm, 1/32W, 0201	MC003351	Resistor, Thin Film, 1K21, 0.1%, ±25ppm, 1/32W, 0201	MC003690
Resistor, Thin Film, 10K, 0.1%, ±50ppm, 1/32W, 0201	MC003480	Resistor, Thin Film, 3K74, 0.1%, ±50ppm, 1/32W, 0201	MC003430
Resistor, Thin Film, 1K43, 0.1%, ±50ppm, 1/32W, 0201	MC003383	Resistor, Thin Film, 88R7, 0.1%, ±50ppm, 1/32W, 0201	MC003786
Resistor, Thin Film, 51R, 0.1%, ±50ppm, 1/32W, 0201	MC003761	Resistor, Thin Film, 93R1, 0.1%, ±50ppm, 1/32W, 0201	MC003789
Resistor, Thin Film, 511R, 0.1%, ±50ppm, 1/32W, 0201	MC003872	Resistor, Thin Film, 127R, 0.1%, ±50ppm, 1/32W, 0201	MC003803
Resistor, Thin Film, 22K, 0.1%, ±50ppm, 1/32W, 0201	MC003516	Resistor, Thin Film, 191R, 0.1%, ±50ppm, 1/32W, 0201	MC003822



multicomp PRO

Description	Part Number	Description	Part Number
Resistor, Thin Film, 95R3, 0.1%, ±25ppm, 1/32W, 0201	MC003028	Resistor, Thin Film, 75R, 0.1%, ±50ppm, 1/32W, 0201	MC003240
Resistor, Thin Film, 1K21, 0.1%, ±25ppm, 1/32W, 0201	MC003152	Resistor, Thin Film, 910R, 0.1%, ±50ppm, 1/32W, 0201	MC003363
Resistor, Thin Film, 2K4, 0.1%, ±25ppm, 1/32W, 0201	MC003183	Resistor, Thin Film, 69R8, 0.1%, ±25ppm, 1/32W, 0201	MC003013
Resistor, Thin Film, 365R, 0.1%, ±50ppm, 1/32W, 0201	MC003316	Resistor, Thin Film, 3K9, 0.1%, ±25ppm, 1/32W, 0201	MC003208
Resistor, Thin Film, 7K15, 0.1%, ±50ppm, 1/32W, 0201	MC004002	Resistor, Thin Film, 78R7, 0.1%, ±50ppm, 1/32W, 0201	MC003242
Resistor, Thin Film, 18K, 0.1%, ±50ppm, 1/32W, 0201	MC004045	Resistor, Thin Film, 13K3, 0.1%, ±50ppm, 1/32W, 0201	MC003493
Resistor, Thin Film, 24K3, 0.1%, ±50ppm, 1/32W, 0201	MC004060	Resistor, Thin Film, 2K49, 0.1%, ±25ppm, 1/32W, 0201	MC003723
Resistor, Thin Film, 267R, 0.1%, ±25ppm, 1/32W, 0201	MC003075	Resistor, Thin Film, 2K87, 0.1%, ±25ppm, 1/32W, 0201	MC003730
Resistor, Thin Film, 316R, 0.1%, ±25ppm, 1/32W, 0201	MC003084	Resistor, Thin Film, 412R, 0.1%, ±50ppm, 1/32W, 0201	MC003860
Resistor, Thin Film, 1K13, 0.1%, ±50ppm, 1/32W, 0201	MC003372	Resistor, Thin Film, 237R, 0.1%, ±50ppm, 1/32W, 0201	MC003293
Resistor, Thin Film, 237R, 0.1%, ±25ppm, 1/32W, 0201	MC003069	Resistor, Thin Film, 1K69, 0.1%, ±50ppm, 1/32W, 0201	MC003391
Resistor, Thin Film, 178R, 0.1%, ±50ppm, 1/32W, 0201	MC003280	Resistor, Thin Film, 226R, 0.1%, ±25ppm, 1/32W, 0201	MC003067
Resistor, Thin Film, 2K61, 0.1%, ±50ppm, 1/32W, 0201	MC003411	Resistor, Thin Film, 1K58, 0.1%, ±25ppm, 1/32W, 0201	MC003163
Resistor, Thin Film, 5K11, 0.1%, ±50ppm, 1/32W, 0201	MC003447	Resistor, Thin Film, 280R, 0.1%, ±50ppm, 1/32W, 0201	MC003302
Resistor, Thin Film, 187R, 0.1%, ±50ppm, 1/32W, 0201	MC003821	Resistor, Thin Film, 24K, 0.1%, ±50ppm, 1/32W, 0201	MC003521
Resistor, Thin Film, 1K3, 0.1%, ±50ppm, 1/32W, 0201	MC003917	Resistor, Thin Film, 80R6, 0.1%, ±25ppm, 1/32W, 0201	MC003557
Resistor, Thin Film, 56R, 0.1%, ±25ppm, 1/32W, 0201	MC003001	Resistor, Thin Film, 649R, 0.1%, ±25ppm, 1/32W, 0201	MC003660
Resistor, Thin Film, 330R, 0.1%, ±25ppm, 1/32W, 0201	MC003086	Resistor, Thin Film, 294R, 0.1%, ±50ppm, 1/32W, 0201	MC003304
Resistor, Thin Film, 174R, 0.1%, ±25ppm, 1/32W, 0201	MC003593	Resistor, Thin Film, 2K05, 0.1%, ±50ppm, 1/32W, 0201	MC003400
Resistor, Thin Film, 86R6, 0.1%, ±25ppm, 1/32W, 0201	MC003561	Resistor, Thin Film, 562R, 0.1%, ±25ppm, 1/32W, 0201	MC003653
Resistor, Thin Film, 620R, 0.1%, ±25ppm, 1/32W, 0201	MC003658	Resistor, Thin Film, 120R, 0.1%, ±25ppm, 1/32W, 0201	MC003576
Resistor, Thin Film, 825R, 0.1%, ±25ppm, 1/32W, 0201	MC003672	Resistor, Thin Film, 130R, 0.1%, ±50ppm, 1/32W, 0201	MC003804
Resistor, Thin Film, 1K33, 0.1%, ±50ppm, 1/32W, 0201	MC003918	Resistor, Thin Film, 953R, 0.1%, ±50ppm, 1/32W, 0201	MC003903
Resistor, Thin Film, 1K91, 0.1%, ±50ppm, 1/32W, 0201	MC003935	Resistor, Thin Film, 1K2, 0.1%, ±25ppm, 1/32W, 0201	MC003689
Resistor, Thin Film, 3K4, 0.1%, ±50ppm, 1/32W, 0201	MC003963	Resistor, Thin Film, 1K78, 0.1%, ±25ppm, 1/32W, 0201	MC003707
Resistor, Thin Film, 6K49, 0.1%, ±50ppm, 1/32W, 0201	MC003459	Resistor, Thin Film, 2K43, 0.1%, ±50ppm, 1/32W, 0201	MC003946
Resistor, Thin Film, 51R1, 0.1%, ±50ppm, 1/32W, 0201	MC003762	Resistor, Thin Film, 1K96, 0.1%, ±50ppm, 1/32W, 0201	MC003398
Resistor, Thin Film, 1K5, 0.1%, ±25ppm, 1/32W, 0201	MC003161	Resistor, Thin Film, 29K4, 0.1%, ±50ppm, 1/32W, 0201	MC003530
Resistor, Thin Film, 16K5, 0.1%, ±50ppm, 1/32W, 0201	MC004041	Resistor, Thin Film, 88R7, 0.1%, ±25ppm, 1/32W, 0201	MC003562
Resistor, Thin Film, 499R, 0.1%, ±25ppm, 1/32W, 0201	MC003108	Resistor, Thin Film, 536R, 0.1%, ±50ppm, 1/32W, 0201	MC003336
Resistor, Thin Film, 62R, 0.1%, ±50ppm, 1/32W, 0201	MC003231	Resistor, Thin Film, 560R, 0.1%, ±50ppm, 1/32W, 0201	MC003338
Resistor, Thin Film, 6K65, 0.1%, ±50ppm, 1/32W, 0201	MC003998	Resistor, Thin Film, 953R, 0.1%, ±50ppm, 1/32W, 0201	MC003365
Resistor, Thin Film, 6K98, 0.1%, ±50ppm, 1/32W, 0201	MC004001	Resistor, Thin Film, 1K33, 0.1%, ±25ppm, 1/32W, 0201	MC003694
Resistor, Thin Film, 9K31, 0.1%, ±50ppm, 1/32W, 0201	MC004015	Resistor, Thin Film, 105R, 0.1%, ±50ppm, 1/32W, 0201	MC003794
Resistor, Thin Film, 324R, 0.1%, ±25ppm, 1/32W, 0201	MC003623	Resistor, Thin Film, 180R, 0.1%, ±50ppm, 1/32W, 0201	MC003819
Resistor, Thin Film, 360R, 0.1%, ±50ppm, 1/32W, 0201	MC003853	Resistor, Thin Film, 6K8, 0.1%, ±50ppm, 1/32W, 0201	MC003461
Resistor, Thin Film, 825R, 0.1%, ±50ppm, 1/32W, 0201	MC003896	Resistor, Thin Film, 16K2, 0.1%, ±50ppm, 1/32W, 0201	MC003502
Resistor, Thin Film, 4K87, 0.1%, ±50ppm, 1/32W, 0201	MC003444	Resistor, Thin Film, 191R, 0.1%, ±25ppm, 1/32W, 0201	MC003598
Resistor, Thin Film, 26K1, 0.1%, ±50ppm, 1/32W, 0201	MC003525	Resistor, Thin Film, 86R6, 0.1%, ±50ppm, 1/32W, 0201	MC003785
Resistor, Thin Film, 118R, 0.1%, ±25ppm, 1/32W, 0201	MC003575	Resistor, Thin Film, 165R, 0.1%, ±50ppm, 1/32W, 0201	MC003815
Resistor, Thin Film, 64R9, 0.1%, ±50ppm, 1/32W, 0201	MC003233	Resistor, Thin Film, 16K, 0.1%, ±50ppm, 1/32W, 0201	MC004039



multicomp PRO

Description	Part Number	Description	Part Number
Resistor, Thin Film, 294R, 0.1%, ±25ppm, 1/32W, 0201	MC003080	Resistor, Thin Film, 2K74, 0.1%, ±25ppm, 1/32W, 0201	MC003728
Resistor, Thin Film, 402R, 0.1%, ±25ppm, 1/32W, 0201	MC003097	Resistor, Thin Film, 2K7, 0.1%, ±50ppm, 1/32W, 0201	MC003413
Resistor, Thin Film, 15K8, 0.1%, ±50ppm, 1/32W, 0201	MC003500	Resistor, Thin Film, 90R9, 0.1%, ±50ppm, 1/32W, 0201	MC003787
Resistor, Thin Film, 24K, 0.1%, ±50ppm, 1/32W, 0201	MC004059	Resistor, Thin Film, 267R, 0.1%, ±50ppm, 1/32W, 0201	MC003837
Resistor, Thin Film, 576R, 0.1%, ±50ppm, 1/32W, 0201	MC003340	Resistor, Thin Film, 68R1, 0.1%, ±50ppm, 1/32W, 0201	MC003236
Resistor, Thin Film, 8K2, 0.1%, ±50ppm, 1/32W, 0201	MC003470	Resistor, Thin Film, 97R6, 0.1%, ±50ppm, 1/32W, 0201	MC003253
Resistor, Thin Film, 1K54, 0.1%, ±50ppm, 1/32W, 0201	MC003924	Resistor, Thin Film, 1K02, 0.1%, ±50ppm, 1/32W, 0201	MC003368
Resistor, Thin Film, 18K2, 0.1%, ±50ppm, 1/32W, 0201	MC004046	Resistor, Thin Film, 4K99, 0.1%, ±50ppm, 1/32W, 0201	MC003983
Resistor, Thin Film, 412R, 0.1%, ±25ppm, 1/32W, 0201	MC003098	Resistor, Thin Film, 1K87, 0.1%, ±25ppm, 1/32W, 0201	MC003172
Resistor, Thin Film, 1K24, 0.1%, ±50ppm, 1/32W, 0201	MC003915	Resistor, Thin Film, 3K16, 0.1%, ±25ppm, 1/32W, 0201	MC003197
Resistor, Thin Film, 7K87, 0.1%, ±50ppm, 1/32W, 0201	MC004006	Resistor, Thin Film, 1K37, 0.1%, ±50ppm, 1/32W, 0201	MC003919
Resistor, Thin Film, 2K32, 0.1%, ±50ppm, 1/32W, 0201	MC003943	Resistor, Thin Film, 23K7, 0.1%, ±50ppm, 1/32W, 0201	MC004058
Resistor, Thin Film, 383R, 0.1%, ±25ppm, 1/32W, 0201	MC003632	Resistor, Thin Film, 24K9, 0.1%, ±50ppm, 1/32W, 0201	MC004061
Resistor, Thin Film, 3K, 0.1%, ±25ppm, 1/32W, 0201	MC003732	Resistor, Thin Film, 59R, 0.1%, ±50ppm, 1/32W, 0201	MC003766
Resistor, Thin Film, 430R, 0.1%, ±50ppm, 1/32W, 0201	MC003862	Resistor, Thin Film, 681R, 0.1%, ±50ppm, 1/32W, 0201	MC003887
Resistor, Thin Film, 487R, 0.1%, ±25ppm, 1/32W, 0201	MC003107	Resistor, Thin Film, 78R7, 0.1%, ±25ppm, 1/32W, 0201	MC003018
Resistor, Thin Film, 4K7, 0.1%, ±25ppm, 1/32W, 0201	MC003218	Resistor, Thin Film, 1K69, 0.1%, ±25ppm, 1/32W, 0201	MC003167
Resistor, Thin Film, 68R, 0.1%, ±50ppm, 1/32W, 0201	MC003235	Resistor, Thin Film, 267R, 0.1%, ±50ppm, 1/32W, 0201	MC003299
Resistor, Thin Film, 270R, 0.1%, ±25ppm, 1/32W, 0201	MC003614	Resistor, Thin Film, 1K82, 0.1%, ±50ppm, 1/32W, 0201	MC003395
Resistor, Thin Film, 348R, 0.1%, ±25ppm, 1/32W, 0201	MC003627	Resistor, Thin Film, 243R, 0.1%, ±50ppm, 1/32W, 0201	MC003295
Resistor, Thin Film, 487R, 0.1%, ±25ppm, 1/32W, 0201	MC003645	Resistor, Thin Film, 432R, 0.1%, ±50ppm, 1/32W, 0201	MC003325
Resistor, Thin Film, 200R, 0.1%, ±25ppm, 1/32W, 0201	MC003600	Resistor, Thin Film, 91R, 0.1%, ±25ppm, 1/32W, 0201	MC003564
Resistor, Thin Film, 4K64, 0.1%, ±25ppm, 1/32W, 0201	MC003755	Resistor, Thin Film, 120R, 0.1%, ±25ppm, 1/32W, 0201	MC003038
Resistor, Thin Film, 4K75, 0.1%, ±25ppm, 1/32W, 0201	MC003757	Resistor, Thin Film, 357R, 0.1%, ±25ppm, 1/32W, 0201	MC003090
Resistor, Thin Film, 2K67, 0.1%, ±50ppm, 1/32W, 0201	MC003950	Resistor, Thin Film, 536R, 0.1%, ±25ppm, 1/32W, 0201	MC003112
Resistor, Thin Film, 31K6, 0.1%, ±50ppm, 1/32W, 0201	MC004071	Resistor, Thin Film, 549R, 0.1%, ±25ppm, 1/32W, 0201	MC003651
Resistor, Thin Film, 33K, 0.1%, ±50ppm, 1/32W, 0201	MC004073	Resistor, Thin Film, 100R, 0.1%, ±50ppm, 1/32W, 0201	MC003792
Resistor, Thin Film, 2K7, 0.1%, ±25ppm, 1/32W, 0201	MC003727	Resistor, Thin Film, 7K5, 0.1%, ±50ppm, 1/32W, 0201	MC004004
Resistor, Thin Film, 523R, 0.1%, $\pm 50 \text{ppm}, 1/32 \text{W}, 0201$	MC003873	Resistor, Thin Film, 3K74, 0.1%, ±25ppm, 1/32W, 0201	MC003206
Resistor, Thin Film, 124R, 0.1%, ±50ppm, 1/32W, 0201	MC003264	Resistor, Thin Film, 1K07, 0.1%, ±50ppm, 1/32W, 0201	MC003370
Resistor, Thin Film, 3K57, 0.1%, ±25ppm, 1/32W, 0201	MC003203	Resistor, Thin Film, 16K9, 0.1%, ±50ppm, 1/32W, 0201	MC003504
Resistor, Thin Film, 4K99, 0.1%, ±25ppm, 1/32W, 0201	MC003221	Resistor, Thin Film, 4K02, 0.1%, ±50ppm, 1/32W, 0201	MC003434
Resistor, Thin Film, 100R, 0.1%, ±50ppm, 1/32W, 0201	MC003254	Resistor, Thin Film, 76R8, 0.1%, ±25ppm, 1/32W, 0201	MC003555
Resistor, Thin Film, 180R, 0.1%, ±50ppm, 1/32W, 0201	MC003281	Resistor, Thin Film, 680R, 0.1%, ±25ppm, 1/32W, 0201	MC003662
Resistor, Thin Film, 348R, 0.1%, ±50ppm, 1/32W, 0201	MC003313	Resistor, Thin Film, 665R, 0.1%, ±50ppm, 1/32W, 0201	MC003885
Resistor, Thin Film, 2K55, 0.1%, ±50ppm, 1/32W, 0201	MC003410	Resistor, Thin Film, 75R, 0.1%, ±25ppm, 1/32W, 0201	MC003016
Resistor, Thin Film, 9K53, 0.1%, ±50ppm, 1/32W, 0201	MC004016	Resistor, Thin Film, 215R, 0.1%, ±25ppm, 1/32W, 0201	MC003065
Resistor, Thin Film, 2K4, 0.1%, ±50ppm, 1/32W, 0201	MC003945	Resistor, Thin Film, 360R, 0.1%, ±25ppm, 1/32W, 0201	MC003629
Resistor, Thin Film, 274R, 0.1%, ±25ppm, 1/32W, 0201	MC003077	Resistor, Thin Film, 392R, 0.1%, ±50ppm, 1/32W, 0201	MC003858
Resistor, Thin Film, 499R, 0.1%, ±50ppm, 1/32W, 0201	MC003332	Resistor, Thin Film, 1K65, 0.1%, ±25ppm, 1/32W, 0201	MC003166
Resistor, Thin Film, 10K2, 0.1%, ±50ppm, 1/32W, 0201	MC003481	Resistor, Thin Film, 3K57, 0.1%, ±50ppm, 1/32W, 0201	MC003427



multicomp PRO

Description	Part Number	Description	Part Number
Resistor, Thin Film, 27K4, 0.1%, ±50ppm, 1/32W, 0201	MC003528	Resistor, Thin Film, 1K5, 0.1%, ±50ppm, 1/32W, 0201	MC003385
Resistor, Thin Film, 634R, 0.1%, ±25ppm, 1/32W, 0201	MC003659	Resistor, Thin Film, 15K4, 0.1%, ±50ppm, 1/32W, 0201	MC003499
Resistor, Thin Film, 866R, 0.1%, ±25ppm, 1/32W, 0201	MC003136	Resistor, Thin Film, 180R, 0.1%, ±25ppm, 1/32W, 0201	MC003595
Resistor, Thin Film, 909R, 0.1%, ±25ppm, 1/32W, 0201	MC003138	Resistor, Thin Film, 732R, 0.1%, ±25ppm, 1/32W, 0201	MC003666
Resistor, Thin Film, 1K8, 0.1%, ±25ppm, 1/32W, 0201	MC003170	Resistor, Thin Film, 1K05, 0.1%, ±25ppm, 1/32W, 0201	MC003683
Resistor, Thin Film, 360R, 0.1%, ±50ppm, 1/32W, 0201	MC003315	Resistor, Thin Film, 80R6, 0.1%, ±50ppm, 1/32W, 0201	MC003781
Resistor, Thin Film, 3K65, 0.1%, ±50ppm, 1/32W, 0201	MC003429	Resistor, Thin Film, 2K74, 0.1%, ±50ppm, 1/32W, 0201	MC003414
Resistor, Thin Film, 60R4, 0.1%, ±25ppm, 1/32W, 0201	MC003543	Resistor, Thin Film, 82R5, 0.1%, ±25ppm, 1/32W, 0201	MC003559
Resistor, Thin Film, 270R, 0.1%, ±50ppm, 1/32W, 0201	MC003300	Resistor, Thin Film, 124R, 0.1%, ±25ppm, 1/32W, 0201	MC003578
Resistor, Thin Film, 3K4, 0.1%, ±50ppm, 1/32W, 0201	MC003425	Resistor, Thin Film, 357R, 0.1%, ±25ppm, 1/32W, 0201	MC003628
Resistor, Thin Film, 3K9, 0.1%, ±50ppm, 1/32W, 0201	MC003432	Resistor, Thin Film, 49R9, 0.1%, ±50ppm, 1/32W, 0201	MC003760
Resistor, Thin Film, 4K22, 0.1%, ±25ppm, 1/32W, 0201	MC003212	Resistor, Thin Film, 287R, 0.1%, ±50ppm, 1/32W, 0201	MC003841
Resistor, Thin Film, 60R4, 0.1%, ±50ppm, 1/32W, 0201	MC003229	Resistor, Thin Film, 1K, 0.1%, ±50ppm, 1/32W, 0201	MC003367
Resistor, Thin Film, 887R, 0.1%, ±50ppm, 1/32W, 0201	MC003361	Resistor, Thin Film, 1K4, 0.1%, ±50ppm, 1/32W, 0201	MC003382
Resistor, Thin Film, 30K1, 0.1%, ±50ppm, 1/32W, 0201	MC003532	Resistor, Thin Film, 1K54, 0.1%, ±50ppm, 1/32W, 0201	MC003386
Resistor, Thin Film, 1K15, 0.1%, ±25ppm, 1/32W, 0201	MC003687	Resistor, Thin Film, 649R, 0.1%, ±25ppm, 1/32W, 0201	MC003122
Resistor, Thin Film, 82R5, 0.1%, ±50ppm, 1/32W, 0201	MC003783	Resistor, Thin Film, 698R, 0.1%, ±50ppm, 1/32W, 0201	MC003350
Resistor, Thin Film, 464R, 0.1%, ±25ppm, 1/32W, 0201	MC003104	Resistor, Thin Film, 7K15, 0.1%, ±50ppm, 1/32W, 0201	MC003464
Resistor, Thin Film, 634R, 0.1%, ±25ppm, 1/32W, 0201	MC003121	Resistor, Thin Film, 6K98, 0.1%, ±50ppm, 1/32W, 0201	MC003463
Resistor, Thin Film, 523R, 0.1%, ±50ppm, 1/32W, 0201	MC003335	Resistor, Thin Film, 267R, 0.1%, ±25ppm, 1/32W, 0201	MC003613
Resistor, Thin Film, 6K04, 0.1%, ±50ppm, 1/32W, 0201	MC003455	Resistor, Thin Film, 1K87, 0.1%, ±25ppm, 1/32W, 0201	MC003710
Resistor, Thin Film, 17K8, 0.1%, ±50ppm, 1/32W, 0201	MC003506	Resistor, Thin Film, 220R, 0.1%, ±50ppm, 1/32W, 0201	MC003828
Resistor, Thin Film, 412R, 0.1%, ±25ppm, 1/32W, 0201	MC003636	Resistor, Thin Film, 232R, 0.1%, ±50ppm, 1/32W, 0201	MC003830
Resistor, Thin Film, 95R3, 0.1%, ±50ppm, 1/32W, 0201	MC003790	Resistor, Thin Film, 8K2, 0.1%, ±50ppm, 1/32W, 0201	MC004008
Resistor, Thin Film, 174R, 0.1%, ±50ppm, 1/32W, 0201	MC003817	Resistor, Thin Film, 20K5, 0.1%, ±50ppm, 1/32W, 0201	MC003513
Resistor, Thin Film, 200R, 0.1%, ±50ppm, 1/32W, 0201	MC003824	Resistor, Thin Film, 3K83, 0.1%, ±25ppm, 1/32W, 0201	MC003745
Resistor, Thin Film, 866R, 0.1%, ±25ppm, 1/32W, 0201	MC003674	Resistor, Thin Film, 4K99, 0.1%, ±25ppm, 1/32W, 0201	MC003759
Resistor, Thin Film, 1K27, 0.1%, ±25ppm, 1/32W, 0201	MC003692	Resistor, Thin Film, 604R, 0.1%, ±25ppm, 1/32W, 0201	MC003656
Resistor, Thin Film, 6K81, 0.1%, ±50ppm, 1/32W, 0201	MC004000	Resistor, Thin Film, 133R, 0.1%, ±50ppm, 1/32W, 0201	MC003805
Resistor, Thin Film, 6K49, 0.1%, ±50ppm, 1/32W, 0201	MC003997	Resistor, Thin Film, 2K, 0.1%, ±50ppm, 1/32W, 0201	MC003937
Resistor, Thin Film, 2K55, 0.1%, ±50ppm, 1/32W, 0201	MC003948	Resistor, Thin Film, 402R, 0.1%, ±50ppm, 1/32W, 0201	MC003859
Resistor, Thin Film, 169R, 0.1%, ±25ppm, 1/32W, 0201	MC003054	Resistor, Thin Film, 536R, 0.1%, ±50ppm, 1/32W, 0201	MC003874
Resistor, Thin Film, 1K47, 0.1%, ±50ppm, 1/32W, 0201	MC003922	Resistor, Thin Film, 4K12, 0.1%, ±50ppm, 1/32W, 0201	MC003973
Resistor, Thin Film, 88R7, 0.1%, ±25ppm, 1/32W, 0201	MC003024	Resistor, Thin Film, 768R, 0.1%, ±50ppm, 1/32W, 0201	MC003892
Resistor, Thin Film, 287R, 0.1%, ±25ppm, 1/32W, 0201	MC003079	Resistor, Thin Film, 845R, 0.1%, ±25ppm, 1/32W, 0201	MC003135
Resistor, Thin Film, 294R, 0.1%, ±50ppm, 1/32W, 0201	MC003842	Resistor, Thin Film, 4K99, 0.1%, ±50ppm, 1/32W, 0201	MC003445
Resistor, Thin Film, 1K15, 0.1%, ±25ppm, 1/32W, 0201	MC003149	Resistor, Thin Film, 10K, 0.1%, ±50ppm, 1/32W, 0201	MC004018
Resistor, Thin Film, 182R, 0.1%, ±50ppm, 1/32W, 0201	MC003282	Resistor, Thin Film, 2K37, 0.1%, ±50ppm, 1/32W, 0201	MC003944
Resistor, Thin Film, 442R, 0.1%, ±50ppm, 1/32W, 0201	MC003864	Resistor, Thin Film, 51R, 0.1%, ±25ppm, 1/32W, 0201	MC002999
Resistor, Thin Film, 100R, 0.1%, ±25ppm, 1/32W, 0201	MC003030	Resistor, Thin Film, 2K74, 0.1%, ±50ppm, 1/32W, 0201	MC003952
Resistor, Thin Film, 3K01, 0.1%, ±50ppm, 1/32W, 0201	MC003419	Resistor, Thin Film, 14K7, 0.1%, ±50ppm, 1/32W, 0201	MC004035



multicomp PRO

Description	Part Number	Description	Part Number
Resistor, Thin Film, 332R, 0.1%, ±25ppm, 1/32W, 0201	MC003087	Resistor, Thin Film, 1K18, 0.1%, ±50ppm, 1/32W, 0201	MC003374
Resistor, Thin Film, 64R9, 0.1%, ±25ppm, 1/32W, 0201	MC003009	Resistor, Thin Film, 8K87, 0.1%, ±50ppm, 1/32W, 0201	MC003474
Resistor, Thin Film, 68R, 0.1%, ±25ppm, 1/32W, 0201	MC003011	Resistor, Thin Film, 316R, 0.1%, ±25ppm, 1/32W, 0201	MC003622
Resistor, Thin Film, 560R, 0.1%, ±25ppm, 1/32W, 0201	MC003114	Resistor, Thin Film, 4K32, 0.1%, ±25ppm, 1/32W, 0201	MC003752
Resistor, Thin Film, 9K76, 0.1%, ±50ppm, 1/32W, 0201	MC004017	Resistor, Thin Film, 620R, 0.1%, ±50ppm, 1/32W, 0201	MC003882
Resistor, Thin Film, 17K8, 0.1%, ±50ppm, 1/32W, 0201	MC004044	Resistor, Thin Film, 1K18, 0.1%, ±25ppm, 1/32W, 0201	MC003150
Resistor, Thin Film, 576R, 0.1%, ±25ppm, 1/32W, 0201	MC003116	Resistor, Thin Film, 27K, 0.1%, ±50ppm, 1/32W, 0201	MC003527
Resistor, Thin Film, 5K49, 0.1%, ±50ppm, 1/32W, 0201	MC003988	Resistor, Thin Film, 845R, 0.1%, ±25ppm, 1/32W, 0201	MC003673
Resistor, Thin Film, 118R, 0.1%, ±25ppm, 1/32W, 0201	MC003037	Resistor, Thin Film, 226R, 0.1%, ±50ppm, 1/32W, 0201	MC003291
Resistor, Thin Film, 143R, 0.1%, ±25ppm, 1/32W, 0201	MC003046	Resistor, Thin Film, 422R, 0.1%, ±50ppm, 1/32W, 0201	MC003323
Resistor, Thin Film, 5K1, 0.1%, ±50ppm, 1/32W, 0201	MC003446	Resistor, Thin Film, 2K26, 0.1%, ±50ppm, 1/32W, 0201	MC003404
Resistor, Thin Film, 59R, 0.1%, ±25ppm, 1/32W, 0201	MC003542	Resistor, Thin Film, 154R, 0.1%, ±25ppm, 1/32W, 0201	MC003587
Resistor, Thin Film, 1K24, 0.1%, ±25ppm, 1/32W, 0201	MC003691	Resistor, Thin Film, 300R, 0.1%, ±25ppm, 1/32W, 0201	MC003619
Resistor, Thin Film, 2K37, 0.1%, ±25ppm, 1/32W, 0201	MC003182	Resistor, Thin Film, 2K32, 0.1%, ±25ppm, 1/32W, 0201	MC003719
Resistor, Thin Film, 121R, 0.1%, ±50ppm, 1/32W, 0201	MC003263	Resistor, Thin Film, 348R, 0.1%, ±50ppm, 1/32W, 0201	MC003851
Resistor, Thin Film, 357R, 0.1%, ±50ppm, 1/32W, 0201	MC003314	Resistor, Thin Film, 619R, 0.1%, ±50ppm, 1/32W, 0201	MC003881
Resistor, Thin Film, 66R5, 0.1%, ±25ppm, 1/32W, 0201	MC003010	Resistor, Thin Film, 82R, 0.1%, ±25ppm, 1/32W, 0201	MC003020
Resistor, Thin Film, 4K3, 0.1%, ±25ppm, 1/32W, 0201	MC003213	Resistor, Thin Film, 4K53, 0.1%, ±50ppm, 1/32W, 0201	MC003978
Resistor, Thin Film, 9K09, 0.1%, ±50ppm, 1/32W, 0201	MC003475	Resistor, Thin Film, 210R, 0.1%, ±50ppm, 1/32W, 0201	MC003288
Resistor, Thin Film, 57R6, 0.1%, ±25ppm, 1/32W, 0201	MC003541	Resistor, Thin Film, 430R, 0.1%, ±50ppm, 1/32W, 0201	MC003324
Resistor, Thin Film, 1K69, 0.1%, ±25ppm, 1/32W, 0201	MC003705	Resistor, Thin Film, 1K74, 0.1%, ±25ppm, 1/32W, 0201	MC003706
Resistor, Thin Film, 1K82, 0.1%, ±25ppm, 1/32W, 0201	MC003709	Resistor, Thin Film, 196R, 0.1%, ±50ppm, 1/32W, 0201	MC003823
Resistor, Thin Film, 18K, 0.1%, ±50ppm, 1/32W, 0201	MC003507	Resistor, Thin Film, 1K4, 0.1%, ±50ppm, 1/32W, 0201	MC003920
Resistor, Thin Film, 150R, 0.1%, ±25ppm, 1/32W, 0201	MC003586	Resistor, Thin Film, 2K32, 0.1%, ±50ppm, 1/32W, 0201	MC003405
Resistor, Thin Film, 158R, 0.1%, ±25ppm, 1/32W, 0201	MC003588	Resistor, Thin Film, 68R1, 0.1%, ±25ppm, 1/32W, 0201	MC003550
Resistor, Thin Film, 91R, 0.1%, ±50ppm, 1/32W, 0201	MC003788	Resistor, Thin Film, 1K5, 0.1%, ±25ppm, 1/32W, 0201	MC003699
Resistor, Thin Film, 453R, 0.1%, ±50ppm, 1/32W, 0201	MC003327	Resistor, Thin Film, 243R, 0.1%, ±25ppm, 1/32W, 0201	MC003071
Resistor, Thin Film, 604R, 0.1%, ±50ppm, 1/32W, 0201	MC003342	Resistor, Thin Film, 340R, 0.1%, ±25ppm, 1/32W, 0201	MC003088
Resistor, Thin Film, 787R, 0.1%, ±25ppm, 1/32W, 0201	MC003131	Resistor, Thin Film, 82R, 0.1%, ±50ppm, 1/32W, 0201	MC003244
Resistor, Thin Film, 620R, 0.1%, ±50ppm, 1/32W, 0201	MC003344	Resistor, Thin Film, 32K4, 0.1%, ±50ppm, 1/32W, 0201	MC003534
Resistor, Thin Film, 12K7, 0.1%, ±50ppm, 1/32W, 0201	MC003491	Resistor, Thin Film, 6K04, 0.1%, ±50ppm, 1/32W, 0201	MC003993
Resistor, Thin Film, 845R, 0.1%, ±50ppm, 1/32W, 0201	MC003359	Resistor, Thin Film, 14K, 0.1%, ±50ppm, 1/32W, 0201	MC004033
Resistor, Thin Film, 2K2, 0.1%, ±25ppm, 1/32W, 0201	MC003717	Resistor, Thin Film, 750R, 0.1%, ±25ppm, 1/32W, 0201	MC003129
Resistor, Thin Film, 324R, 0.1%, ±50ppm, 1/32W, 0201	MC003847	Resistor, Thin Film, 118R, 0.1%, ±50ppm, 1/32W, 0201	MC003261
Resistor, Thin Film, 430R, 0.1%, ±25ppm, 1/32W, 0201	MC003638	Resistor, Thin Film, 1K21, 0.1%, ±50ppm, 1/32W, 0201	MC003376
Resistor, Thin Film, 464R, 0.1%, ±50ppm, 1/32W, 0201	MC003866	Resistor, Thin Film, 28K, 0.1%, ±50ppm, 1/32W, 0201	MC004067
Resistor, Thin Film, 931R, 0.1%, ±25ppm, 1/32W, 0201	MC003140	Resistor, Thin Film, 49R9, 0.1%, ±25ppm, 1/32W, 0201	MC002998
Resistor, Thin Film, 182R, 0.1%, ±50ppm, 1/32W, 0201	MC003820	Resistor, Thin Film, 249R, 0.1%, ±25ppm, 1/32W, 0201	MC003072
Resistor, Thin Film, 6K8, 0.1%, ±50ppm, 1/32W, 0201	MC003999	Resistor, Thin Film, 8K45, 0.1%, ±50ppm, 1/32W, 0201	MC003472
Resistor, Thin Film, 3K32, 0.1%, ±50ppm, 1/32W, 0201	MC003962	Resistor, Thin Film, 4K3, 0.1%, ±25ppm, 1/32W, 0201	MC003751
Resistor, Thin Film, 84R5, 0.1%, ±50ppm, 1/32W, 0201	MC003246	Resistor, Thin Film, 61R9, 0.1%, ±50ppm, 1/32W, 0201	MC003768



multicomp PRO

Description	Part Number	Description	Part Number
Resistor, Thin Film, 768R, 0.1%, ±25ppm, 1/32W, 0201	MC003130	Resistor, Thin Film, 8K45, 0.1%, ±50ppm, 1/32W, 0201	MC004010
Resistor, Thin Film, 4K12, 0.1%, ±25ppm, 1/32W, 0201	MC003211	Resistor, Thin Film, 76R8, 0.1%, ±50ppm, 1/32W, 0201	MC003779
Resistor, Thin Film, 82R5, 0.1%, ±50ppm, 1/32W, 0201	MC003245	Resistor, Thin Film, 110R, 0.1%, ±50ppm, 1/32W, 0201	MC003796
Resistor, Thin Film, 158R, 0.1%, ±50ppm, 1/32W, 0201	MC003812	Resistor, Thin Film, 12K1, 0.1%, ±50ppm, 1/32W, 0201	MC004027
Resistor, Thin Film, 130R, 0.1%, ±25ppm, 1/32W, 0201	MC003042	Resistor, Thin Film, 1K24, 0.1%, ±50ppm, 1/32W, 0201	MC003377
Resistor, Thin Film, 681R, 0.1%, ±25ppm, 1/32W, 0201	MC003125	Resistor, Thin Film, 422R, 0.1%, ±25ppm, 1/32W, 0201	MC003637
Resistor, Thin Film, 12K1, 0.1%, ±50ppm, 1/32W, 0201	MC003489	Resistor, Thin Film, 3K01, 0.1%, ±25ppm, 1/32W, 0201	MC003733
Resistor, Thin Film, 160R, 0.1%, ±25ppm, 1/32W, 0201	MC003589	Resistor, Thin Film, 56R2, 0.1%, ±50ppm, 1/32W, 0201	MC003226
Resistor, Thin Film, 232R, 0.1%, ±25ppm, 1/32W, 0201	MC003606	Resistor, Thin Film, 61R9, 0.1%, ±50ppm, 1/32W, 0201	MC003230
Resistor, Thin Film, 634R, 0.1%, ±50ppm, 1/32W, 0201	MC003883	Resistor, Thin Film, 115R, 0.1%, ±50ppm, 1/32W, 0201	MC003260
Resistor, Thin Film, 4K75, 0.1%, ±50ppm, 1/32W, 0201	MC003981	Resistor, Thin Film, 432R, 0.1%, ±25ppm, 1/32W, 0201	MC003639
Resistor, Thin Film, 2K94, 0.1%, ±25ppm, 1/32W, 0201	MC003193	Resistor, Thin Film, 845R, 0.1%, ±50ppm, 1/32W, 0201	MC003897
Resistor, Thin Film, 1K37, 0.1%, ±25ppm, 1/32W, 0201	MC003157	Resistor, Thin Film, 162R, 0.1%, ±25ppm, 1/32W, 0201	MC003052
Resistor, Thin Film, 316R, 0.1%, ±50ppm, 1/32W, 0201	MC003308	Resistor, Thin Film, 6K19, 0.1%, ±50ppm, 1/32W, 0201	MC003456
Resistor, Thin Film, 4K22, 0.1%, ±50ppm, 1/32W, 0201	MC003436	Resistor, Thin Film, 2K37, 0.1%, ±25ppm, 1/32W, 0201	MC003720
Resistor, Thin Film, 976R, 0.1%, ±25ppm, 1/32W, 0201	MC003142	Resistor, Thin Film, 340R, 0.1%, ±50ppm, 1/32W, 0201	MC003850
Resistor, Thin Film, 1K43, 0.1%, ±25ppm, 1/32W, 0201	MC003159	Resistor, Thin Film, 649R, 0.1%, ±50ppm, 1/32W, 0201	MC003884
Resistor, Thin Film, 2K8, 0.1%, ±25ppm, 1/32W, 0201	MC003191	Resistor, Thin Film, 5K62, 0.1%, ±50ppm, 1/32W, 0201	MC003452
Resistor, Thin Film, 442R, 0.1%, ±50ppm, 1/32W, 0201	MC003326	Resistor, Thin Film, 71R5, 0.1%, ±25ppm, 1/32W, 0201	MC003552
Resistor, Thin Film, 619R, 0.1%, ±50ppm, 1/32W, 0201	MC003343	Resistor, Thin Film, 453R, 0.1%, ±50ppm, 1/32W, 0201	MC003865
Resistor, Thin Film, 866R, 0.1%, ±50ppm, 1/32W, 0201	MC003360	Resistor, Thin Film, 200R, 0.1%, ±25ppm, 1/32W, 0201	MC003062
Resistor, Thin Film, 402R, 0.1%, ±50ppm, 1/32W, 0201	MC003321	Resistor, Thin Film, 3K, 0.1%, ±25ppm, 1/32W, 0201	MC003194
Resistor, Thin Film, 69R8, 0.1%, ±25ppm, 1/32W, 0201	MC003551	Resistor, Thin Film, 97R6, 0.1%, ±25ppm, 1/32W, 0201	MC003567
Resistor, Thin Film, 100R, 0.1%, ±25ppm, 1/32W, 0201	MC003568	Resistor, Thin Film, 511R, 0.1%, ±25ppm, 1/32W, 0201	MC003648
Resistor, Thin Film, 4K32, 0.1%, ±50ppm, 1/32W, 0201	MC003438	Resistor, Thin Film, 1K02, 0.1%, ±25ppm, 1/32W, 0201	MC003682
Resistor, Thin Film, 23K2, 0.1%, ±50ppm, 1/32W, 0201	MC003519	Resistor, Thin Film, 2K, 0.1%, ±25ppm, 1/32W, 0201	MC003175
Resistor, Thin Film, 698R, 0.1%, ±25ppm, 1/32W, 0201	MC003664	Resistor, Thin Film, 300R, 0.1%, ±50ppm, 1/32W, 0201	MC003305
Resistor, Thin Film, 909R, 0.1%, $\pm 50 \text{ppm}, 1/32 \text{W}, 0201$	MC003900	Resistor, Thin Film, 113R, 0.1%, ±50ppm, 1/32W, 0201	MC003797
Resistor, Thin Film, 4K64, 0.1%, ±50ppm, 1/32W, 0201	MC003979	Resistor, Thin Film, 510R, 0.1%, ±25ppm, 1/32W, 0201	MC003647
Resistor, Thin Film, 165R, 0.1%, ±25ppm, 1/32W, 0201	MC003053	Resistor, Thin Film, 1K54, 0.1%, ±25ppm, 1/32W, 0201	MC003700
Resistor, Thin Film, 150R, 0.1%, ±50ppm, 1/32W, 0201	MC003272	Resistor, Thin Film, 30K, 0.1%, ±50ppm, 1/32W, 0201	MC004069
Resistor, Thin Film, 158R, 0.1%, ±50ppm, 1/32W, 0201	MC003274	Resistor, Thin Film, 3K09, 0.1%, ±50ppm, 1/32W, 0201	MC003420
Resistor, Thin Film, 95R3, 0.1%, ±25ppm, 1/32W, 0201	MC003566	Resistor, Thin Film, 3K24, 0.1%, ±50ppm, 1/32W, 0201	MC003422
Resistor, Thin Film, 4K32, 0.1%, ±25ppm, 1/32W, 0201	MC003214	Resistor, Thin Film, 31K6, 0.1%, ±50ppm, 1/32W, 0201	MC003533
Resistor, Thin Film, 14K3, 0.1%, ±50ppm, 1/32W, 0201	MC003496	Resistor, Thin Film, 237R, 0.1%, ±50ppm, 1/32W, 0201	MC003831
Resistor, Thin Film, 147R, 0.1%, ±25ppm, 1/32W, 0201	MC003585	Resistor, Thin Film, 11K5, 0.1%, ±50ppm, 1/32W, 0201	MC004024
Resistor, Thin Film, 6K34, 0.1%, ±50ppm, 1/32W, 0201	MC003458	Resistor, Thin Film, 15K, 0.1%, ±50ppm, 1/32W, 0201	MC004036
Resistor, Thin Film, 17K4, 0.1%, ±50ppm, 1/32W, 0201	MC003505	Resistor, Thin Film, 162R, 0.1%, ±50ppm, 1/32W, 0201	MC003814
Resistor, Thin Film, 215R, 0.1%, ±25ppm, 1/32W, 0201	MC003603	Resistor, Thin Film, 12K, 0.1%, ±50ppm, 1/32W, 0201	MC004026
Resistor, Thin Film, 1K15, 0.1%, ±50ppm, 1/32W, 0201	MC003911	Resistor, Thin Film, 2K8, 0.1%, ±50ppm, 1/32W, 0201	MC003953
Resistor, Thin Film, 1K65, 0.1%, ±50ppm, 1/32W, 0201	MC003928	Resistor, Thin Film, 5K76, 0.1%, ±50ppm, 1/32W, 0201	MC003453



multicomp PRO

Description	Part Number	Description	Part Number
Resistor, Thin Film, 523R, 0.1%, ±25ppm, 1/32W, 0201	MC003649	Resistor, Thin Film, 7K68, 0.1%, ±50ppm, 1/32W, 0201	MC003467
Resistor, Thin Film, 115R, 0.1%, ±50ppm, 1/32W, 0201	MC003798	Resistor, Thin Film, 270R, 0.1%, ±50ppm, 1/32W, 0201	MC003838
Resistor, Thin Film, 51R1, 0.1%, ±25ppm, 1/32W, 0201	MC003000	Resistor, Thin Film, 73R2, 0.1%, ±25ppm, 1/32W, 0201	MC003015
Resistor, Thin Film, 63R4, 0.1%, ±25ppm, 1/32W, 0201	MC003008	Resistor, Thin Film, 2K7, 0.1%, ±25ppm, 1/32W, 0201	MC003189
Resistor, Thin Film, 562R, 0.1%, ±25ppm, 1/32W, 0201	MC003115	Resistor, Thin Film, 4K7, 0.1%, ±50ppm, 1/32W, 0201	MC003442
Resistor, Thin Film, 1K8, 0.1%, ±25ppm, 1/32W, 0201	MC003708	Resistor, Thin Film, 910R, 0.1%, ±25ppm, 1/32W, 0201	MC003677
Resistor, Thin Film, 976R, 0.1%, ±50ppm, 1/32W, 0201	MC003904	Resistor, Thin Film, 1K58, 0.1%, ±50ppm, 1/32W, 0201	MC003925
Resistor, Thin Film, 1K96, 0.1%, ±50ppm, 1/32W, 0201	MC003936	Resistor, Thin Film, 8K06, 0.1%, ±50ppm, 1/32W, 0201	MC004007
Resistor, Thin Film, 287R, 0.1%, ±25ppm, 1/32W, 0201	MC003617	Resistor, Thin Film, 8K25, 0.1%, ±50ppm, 1/32W, 0201	MC004009
Resistor, Thin Film, 330R, 0.1%, ±25ppm, 1/32W, 0201	MC003624	Resistor, Thin Film, 60R4, 0.1%, ±50ppm, 1/32W, 0201	MC003767
Resistor, Thin Film, 2K94, 0.1%, ±25ppm, 1/32W, 0201	MC003731	Resistor, Thin Film, 910R, 0.1%, ±50ppm, 1/32W, 0201	MC003901
Resistor, Thin Film, 27K4, 0.1%, ±50ppm, 1/32W, 0201	MC004066	Resistor, Thin Film, 953R, 0.1%, ±25ppm, 1/32W, 0201	MC003141
Resistor, Thin Film, 30K1, 0.1%, ±50ppm, 1/32W, 0201	MC004070	Resistor, Thin Film, 2K2, 0.1%, ±50ppm, 1/32W, 0201	MC003941
Resistor, Thin Film, 523R, 0.1%, ±25ppm, 1/32W, 0201	MC003111	Resistor, Thin Film, 2K7, 0.1%, ±50ppm, 1/32W, 0201	MC003951
Resistor, Thin Film, 536R, 0.1%, ±25ppm, 1/32W, 0201	MC003650	Resistor, Thin Film, 140R, 0.1%, ±25ppm, 1/32W, 0201	MC003045
Resistor, Thin Film, 715R, 0.1%, ±25ppm, 1/32W, 0201	MC003665	Resistor, Thin Film, 73R2, 0.1%, ±50ppm, 1/32W, 0201	MC003777
Resistor, Thin Film, 750R, 0.1%, ±25ppm, 1/32W, 0201	MC003667	Resistor, Thin Film, 215R, 0.1%, ±50ppm, 1/32W, 0201	MC003827
Resistor, Thin Film, 196R, 0.1%, ±25ppm, 1/32W, 0201	MC003061	Resistor, Thin Film, 7K32, 0.1%, ±50ppm, 1/32W, 0201	MC004003
Resistor, Thin Film, 13K, 0.1%, ±50ppm, 1/32W, 0201	MC003492	Resistor, Thin Film, 154R, 0.1%, ±50ppm, 1/32W, 0201	MC003811
Resistor, Thin Film, 16K5, 0.1%, ±50ppm, 1/32W, 0201	MC003503	Resistor, Thin Film, 1K6, 0.1%, ±50ppm, 1/32W, 0201	MC003926
Resistor, Thin Film, 590R, 0.1%, ±50ppm, 1/32W, 0201	MC003341	Resistor, Thin Film, 2K87, 0.1%, ±50ppm, 1/32W, 0201	MC003954
Resistor, Thin Film, 825R, 0.1%, ±50ppm, 1/32W, 0201	MC003358	Resistor, Thin Film, 432R, 0.1%, ±50ppm, 1/32W, 0201	MC003863
Resistor, Thin Film, 1K2, 0.1%, ±50ppm, 1/32W, 0201	MC003375	Resistor, Thin Film, 698R, 0.1%, ±50ppm, 1/32W, 0201	MC003888
Resistor, Thin Film, 4K42, 0.1%, ±50ppm, 1/32W, 0201	MC003977	Resistor, Thin Film, 110R, 0.1%, ±25ppm, 1/32W, 0201	MC003034
Resistor, Thin Film, 1K24, 0.1%, ±25ppm, 1/32W, 0201	MC003153	Resistor, Thin Film, 309R, 0.1%, ±25ppm, 1/32W, 0201	MC003083
Resistor, Thin Film, 1K6, 0.1%, ±25ppm, 1/32W, 0201	MC003164	Resistor, Thin Film, 3K32, 0.1%, ±25ppm, 1/32W, 0201	MC003200
Resistor, Thin Film, 56R, 0.1%, ±50ppm, 1/32W, 0201	MC003225	Resistor, Thin Film, 73R2, 0.1%, ±50ppm, 1/32W, 0201	MC003239
Resistor, Thin Film, 91R, 0.1%, ±50ppm, 1/32W, 0201	MC003250	Resistor, Thin Film, 732R, 0.1%, ±25ppm, 1/32W, 0201	MC003128
Resistor, Thin Film, 6K65, 0.1%, ±50ppm, 1/32W, 0201	MC003460	Resistor, Thin Film, 11K, 0.1%, ±50ppm, 1/32W, 0201	MC003484
Resistor, Thin Film, 330R, 0.1%, ±50ppm, 1/32W, 0201	MC003310	Resistor, Thin Film, 11K5, 0.1%, ±50ppm, 1/32W, 0201	MC003486
Resistor, Thin Film, 2K, 0.1%, ±50ppm, 1/32W, 0201	MC003399	Resistor, Thin Film, 1K27, 0.1%, ±50ppm, 1/32W, 0201	MC003378
Resistor, Thin Film, 2K94, 0.1%, ±50ppm, 1/32W, 0201	MC003417	Resistor, Thin Film, 1K62, 0.1%, ±50ppm, 1/32W, 0201	MC003389
Resistor, Thin Film, 22K1, 0.1%, ±50ppm, 1/32W, 0201	MC003517	Resistor, Thin Film, 169R, 0.1%, ±25ppm, 1/32W, 0201	MC003592
Resistor, Thin Film, 402R, 0.1%, ±25ppm, 1/32W, 0201	MC003635	Resistor, Thin Film, 1K, 0.1%, ±25ppm, 1/32W, 0201	MC003143
Resistor, Thin Film, 464R, 0.1%, ±25ppm, 1/32W, 0201	MC003642	Resistor, Thin Film, 1K4, 0.1%, ±25ppm, 1/32W, 0201	MC003158
Resistor, Thin Film, 301R, 0.1%, ±25ppm, 1/32W, 0201	MC003620	Resistor, Thin Film, 2K87, 0.1%, ±25ppm, 1/32W, 0201	MC003192
Resistor, Thin Film, 2K15, 0.1%, ±25ppm, 1/32W, 0201	MC003716	Resistor, Thin Film, 18K7, 0.1%, ±50ppm, 1/32W, 0201	MC004047
Resistor, Thin Film, 3K16, 0.1%, ±25ppm, 1/32W, 0201	MC003735	Resistor, Thin Film, 27K, 0.1%, ±50ppm, 1/32W, 0201	MC004065
Resistor, Thin Film, 23K7, 0.1%, ±50ppm, 1/32W, 0201	MC003520	Resistor, Thin Film, 133R, 0.1%, ±25ppm, 1/32W, 0201	MC003043
Resistor, Thin Film, 169R, 0.1%, ±50ppm, 1/32W, 0201	MC003816	Resistor, Thin Film, 210R, 0.1%, ±25ppm, 1/32W, 0201	MC003064
Resistor, Thin Film, 1K, 0.1%, ±50ppm, 1/32W, 0201	MC003905	Resistor, Thin Film, 1K82, 0.1%, ±25ppm, 1/32W, 0201	MC003171



multicomp PRO

Description	Part Number	Description	Part Number
Resistor, Thin Film, 30K, 0.1%, ±50ppm, 1/32W, 0201	MC003531	Resistor, Thin Film, 14K3, 0.1%, ±50ppm, 1/32W, 0201	MC004034
Resistor, Thin Film, 240R, 0.1%, ±25ppm, 1/32W, 0201	MC003070	Resistor, Thin Film, 29K4, 0.1%, ±50ppm, 1/32W, 0201	MC004068
Resistor, Thin Film, 59R, 0.1%, ±50ppm, 1/32W, 0201	MC003228	Resistor, Thin Film, 3K6, 0.1%, ±50ppm, 1/32W, 0201	MC003966
Resistor, Thin Film, 12K, 0.1%, ±50ppm, 1/32W, 0201	MC003488	Resistor, Thin Film, 169R, 0.1%, ±50ppm, 1/32W, 0201	MC003278
Resistor, Thin Film, 147R, 0.1%, ±50ppm, 1/32W, 0201	MC003271	Resistor, Thin Film, 287R, 0.1%, ±50ppm, 1/32W, 0201	MC003303
Resistor, Thin Film, 412R, 0.1%, ±50ppm, 1/32W, 0201	MC003322	Resistor, Thin Film, 59R, 0.1%, ±25ppm, 1/32W, 0201	MC003004
Resistor, Thin Film, 107R, 0.1%, ±50ppm, 1/32W, 0201	MC003795	Resistor, Thin Film, 383R, 0.1%, ±25ppm, 1/32W, 0201	MC003094
Resistor, Thin Film, 226R, 0.1%, ±25ppm, 1/32W, 0201	MC003605	Resistor, Thin Film, 432R, 0.1%, ±25ppm, 1/32W, 0201	MC003101
Resistor, Thin Film, 2K26, 0.1%, ±25ppm, 1/32W, 0201	MC003718	Resistor, Thin Film, 191R, 0.1%, ±25ppm, 1/32W, 0201	MC003060
Resistor, Thin Film, 62R, 0.1%, ±50ppm, 1/32W, 0201	MC003769	Resistor, Thin Film, 634R, 0.1%, ±50ppm, 1/32W, 0201	MC003345
Resistor, Thin Film, 280R, 0.1%, ±25ppm, 1/32W, 0201	MC003616	Resistor, Thin Film, 1K37, 0.1%, ±50ppm, 1/32W, 0201	MC003381
Resistor, Thin Film, 470R, 0.1%, ±25ppm, 1/32W, 0201	MC003643	Resistor, Thin Film, 2K37, 0.1%, ±50ppm, 1/32W, 0201	MC003406
Resistor, Thin Film, 1K96, 0.1%, ±25ppm, 1/32W, 0201	MC003712	Resistor, Thin Film, 90R9, 0.1%, ±25ppm, 1/32W, 0201	MC003563
Resistor, Thin Film, 78R7, 0.1%, ±25ppm, 1/32W, 0201	MC003556	Resistor, Thin Film, 12K4, 0.1%, ±50ppm, 1/32W, 0201	MC004028
Resistor, Thin Film, 97R6, 0.1%, ±50ppm, 1/32W, 0201	MC003791	Resistor, Thin Film, 19K1, 0.1%, ±50ppm, 1/32W, 0201	MC003510
Resistor, Thin Film, 124R, 0.1%, ±50ppm, 1/32W, 0201	MC003802	Resistor, Thin Film, 4K12, 0.1%, ±25ppm, 1/32W, 0201	MC003749
Resistor, Thin Film, 1K18, 0.1%, ±50ppm, 1/32W, 0201	MC003912	Resistor, Thin Film, 562R, 0.1%, ±50ppm, 1/32W, 0201	MC003877
Resistor, Thin Film, 1K69, 0.1%, ±50ppm, 1/32W, 0201	MC003929	Resistor, Thin Film, 910R, 0.1%, ±25ppm, 1/32W, 0201	MC003139
Resistor, Thin Film, 5K9, 0.1%, ±50ppm, 1/32W, 0201	MC003992	Resistor, Thin Film, 232R, 0.1%, ±50ppm, 1/32W, 0201	MC003292
Resistor, Thin Film, 590R, 0.1%, ±25ppm, 1/32W, 0201	MC003117	Resistor, Thin Film, 374R, 0.1%, ±50ppm, 1/32W, 0201	MC003317
Resistor, Thin Film, 4K64, 0.1%, ±25ppm, 1/32W, 0201	MC003217	Resistor, Thin Film, 1K6, 0.1%, ±50ppm, 1/32W, 0201	MC003388
Resistor, Thin Film, 49R9, 0.1%, ±50ppm, 1/32W, 0201	MC003222	Resistor, Thin Film, 137R, 0.1%, ±25ppm, 1/32W, 0201	MC003582
Resistor, Thin Film, 470R, 0.1%, ±50ppm, 1/32W, 0201	MC003867	Resistor, Thin Film, 237R, 0.1%, ±25ppm, 1/32W, 0201	MC003607
Resistor, Thin Film, 80R6, 0.1%, ±25ppm, 1/32W, 0201	MC003019	Resistor, Thin Film, 294R, 0.1%, ±25ppm, 1/32W, 0201	MC003618
Resistor, Thin Film, 4K3, 0.1%, ±50ppm, 1/32W, 0201	MC003437	Resistor, Thin Film, 3K4, 0.1%, ±25ppm, 1/32W, 0201	MC003739
Resistor, Thin Film, 196R, 0.1%, ±25ppm, 1/32W, 0201	MC003599	Resistor, Thin Film, 510R, 0.1%, ±50ppm, 1/32W, 0201	MC003871
Resistor, Thin Film, 2K, 0.1%, ±25ppm, 1/32W, 0201	MC003713	Resistor, Thin Film, 68R1, 0.1%, ±25ppm, 1/32W, 0201	MC003012
Resistor, Thin Film, 499R, 0.1%, ±50ppm, 1/32W, 0201	MC003870	Resistor, Thin Film, 3K83, 0.1%, ±25ppm, 1/32W, 0201	MC003207
Resistor, Thin Film, 1K5, 0.1%, ±50ppm, 1/32W, 0201	MC003923	Resistor, Thin Film, 107R, 0.1%, ±50ppm, 1/32W, 0201	MC003257
Resistor, Thin Film, 10K7, 0.1%, ±50ppm, 1/32W, 0201	MC004021	Resistor, Thin Film, 9K76, 0.1%, ±50ppm, 1/32W, 0201	MC003479
Resistor, Thin Film, 3K57, 0.1%, ±50ppm, 1/32W, 0201	MC003965	Resistor, Thin Film, 18K7, 0.1%, ±50ppm, 1/32W, 0201	MC003509
Resistor, Thin Film, 51R1, 0.1%, ±50ppm, 1/32W, 0201	MC003224	Resistor, Thin Film, 143R, 0.1%, ±25ppm, 1/32W, 0201	MC003584
Resistor, Thin Film, 86R6, 0.1%, ±50ppm, 1/32W, 0201	MC003247	Resistor, Thin Film, 360R, 0.1%, ±25ppm, 1/32W, 0201	MC003091
Resistor, Thin Film, 768R, 0.1%, ±50ppm, 1/32W, 0201	MC003354	Resistor, Thin Film, 698R, 0.1%, ±25ppm, 1/32W, 0201	MC003126
Resistor, Thin Film, 20K5, 0.1%, ±50ppm, 1/32W, 0201	MC004051	Resistor, Thin Film, 4K42, 0.1%, ±25ppm, 1/32W, 0201	MC003215
Resistor, Thin Film, 93R1, 0.1%, ±25ppm, 1/32W, 0201	MC003027	Resistor, Thin Film, 464R, 0.1%, ±50ppm, 1/32W, 0201	MC003328
Resistor, Thin Film, 270R, 0.1%, ±25ppm, 1/32W, 0201	MC003076	Resistor, Thin Film, 1K1, 0.1%, ±50ppm, 1/32W, 0201	MC003371
Resistor, Thin Film, 22K6, 0.1%, ±50ppm, 1/32W, 0201	MC003518	Resistor, Thin Film, 2K55, 0.1%, ±25ppm, 1/32W, 0201	MC003724
Resistor, Thin Film, 976R, 0.1%, ±25ppm, 1/32W, 0201	MC003680	Resistor, Thin Film, 105R, 0.1%, ±50ppm, 1/32W, 0201	MC003256
Resistor, Thin Film, 1K43, 0.1%, ±25ppm, 1/32W, 0201	MC003697	Resistor, Thin Film, 1K3, 0.1%, ±50ppm, 1/32W, 0201	MC003379
Resistor, Thin Film, 1K62, 0.1%, ±50ppm, 1/32W, 0201	MC003927	Resistor, Thin Film, 3K3, 0.1%, ±25ppm, 1/32W, 0201	MC003737



multicomp PRO

Description	Part Number	Description	Part Number
Resistor, Thin Film, 243R, 0.1%, ±25ppm, 1/32W, 0201	MC003609	Resistor, Thin Film, 147R, 0.1%, ±50ppm, 1/32W, 0201	MC003809
Resistor, Thin Film, 487R, 0.1%, ±50ppm, 1/32W, 0201	MC003869	Resistor, Thin Film, 1K27, 0.1%, ±50ppm, 1/32W, 0201	MC003916
Resistor, Thin Film, 3K65, 0.1%, ±50ppm, 1/32W, 0201	MC003967	Resistor, Thin Film, 16K2, 0.1%, ±50ppm, 1/32W, 0201	MC004040
Resistor, Thin Film, 158R, 0.1%, ±25ppm, 1/32W, 0201	MC003050	Resistor, Thin Film, 22K, 0.1%, ±50ppm, 1/32W, 0201	MC004054
Resistor, Thin Film, 165R, 0.1%, ±50ppm, 1/32W, 0201	MC003277	Resistor, Thin Film, 6K34, 0.1%, ±50ppm, 1/32W, 0201	MC003996
Resistor, Thin Film, 2K87, 0.1%, ±50ppm, 1/32W, 0201	MC003416	Resistor, Thin Film, 619R, 0.1%, ±25ppm, 1/32W, 0201	MC003119
Resistor, Thin Film, 604R, 0.1%, ±50ppm, 1/32W, 0201	MC003880	Resistor, Thin Film, 90R9, 0.1%, ±50ppm, 1/32W, 0201	MC003249
Resistor, Thin Film, 1K1, 0.1%, ±25ppm, 1/32W, 0201	MC003147	Resistor, Thin Film, 261R, 0.1%, ±25ppm, 1/32W, 0201	MC003074
Resistor, Thin Film, 2K4, 0.1%, ±50ppm, 1/32W, 0201	MC003407	Resistor, Thin Film, 715R, 0.1%, ±25ppm, 1/32W, 0201	MC003127
Resistor, Thin Film, 56R, 0.1%, ±25ppm, 1/32W, 0201	MC003539	Resistor, Thin Film, 76R8, 0.1%, ±50ppm, 1/32W, 0201	MC003241
Resistor, Thin Film, 63R4, 0.1%, ±25ppm, 1/32W, 0201	MC003546	Resistor, Thin Film, 392R, 0.1%, ±50ppm, 1/32W, 0201	MC003320
Resistor, Thin Film, 1K82, 0.1%, ±50ppm, 1/32W, 0201	MC003933	Resistor, Thin Film, 107R, 0.1%, ±25ppm, 1/32W, 0201	MC003571
Resistor, Thin Film, 499R, 0.1%, ±25ppm, 1/32W, 0201	MC003646	Resistor, Thin Film, 130R, 0.1%, ±25ppm, 1/32W, 0201	MC003580
Resistor, Thin Film, 909R, 0.1%, ±25ppm, 1/32W, 0201	MC003676	Resistor, Thin Film, 806R, 0.1%, ±50ppm, 1/32W, 0201	MC003356
Resistor, Thin Film, 150R, 0.1%, ±50ppm, 1/32W, 0201	MC003810	Resistor, Thin Film, 453R, 0.1%, ±25ppm, 1/32W, 0201	MC003641
Resistor, Thin Film, 4K7, 0.1%, ±25ppm, 1/32W, 0201	MC003756	Resistor, Thin Film, 3K57, 0.1%, ±25ppm, 1/32W, 0201	MC003741
Resistor, Thin Film, 56R, 0.1%, ±50ppm, 1/32W, 0201	MC003763	Resistor, Thin Film, 549R, 0.1%, ±50ppm, 1/32W, 0201	MC003337
Resistor, Thin Film, 3K09, 0.1%, ±25ppm, 1/32W, 0201	MC003196	Resistor, Thin Film, 787R, 0.1%, ±50ppm, 1/32W, 0201	MC003355
Resistor, Thin Film, 64R9, 0.1%, ±50ppm, 1/32W, 0201	MC003771	Resistor, Thin Film, 1K33, 0.1%, ±50ppm, 1/32W, 0201	MC003380
Resistor, Thin Film, 68R, 0.1%, ±50ppm, 1/32W, 0201	MC003773	Resistor, Thin Film, 374R, 0.1%, ±25ppm, 1/32W, 0201	MC003093
Resistor, Thin Film, 1K27, 0.1%, ±25ppm, 1/32W, 0201	MC003154	Resistor, Thin Film, 665R, 0.1%, ±50ppm, 1/32W, 0201	MC003347
Resistor, Thin Film, 301R, 0.1%, ±50ppm, 1/32W, 0201	MC003844	Resistor, Thin Film, 5K9, 0.1%, ±50ppm, 1/32W, 0201	MC003454
Resistor, Thin Film, 316R, 0.1%, ±50ppm, 1/32W, 0201	MC003846	Resistor, Thin Film, 787R, 0.1%, ±25ppm, 1/32W, 0201	MC003669
Resistor, Thin Film, 576R, 0.1%, ±50ppm, 1/32W, 0201	MC003878	Resistor, Thin Film, 931R, 0.1%, ±25ppm, 1/32W, 0201	MC003678
Resistor, Thin Film, 51R1, 0.1%, ±25ppm, 1/32W, 0201	MC003538	Resistor, Thin Film, 143R, 0.1%, ±50ppm, 1/32W, 0201	MC003808
Resistor, Thin Film, 1K6, 0.1%, ±25ppm, 1/32W, 0201	MC003702	Resistor, Thin Film, 1K58, 0.1%, ±50ppm, 1/32W, 0201	MC003387
Resistor, Thin Film, 84R5, 0.1%, ±50ppm, 1/32W, 0201	MC003784	Resistor, Thin Film, 16K, 0.1%, ±50ppm, 1/32W, 0201	MC003501
Resistor, Thin Film, 9K09, 0.1%, ±50ppm, 1/32W, 0201	MC004013	Resistor, Thin Film, 20K, 0.1%, ±50ppm, 1/32W, 0201	MC003512
Resistor, Thin Film, 23K2, 0.1%, ±50ppm, 1/32W, 0201	MC004057	Resistor, Thin Film, 332R, 0.1%, ±50ppm, 1/32W, 0201	MC003311
Resistor, Thin Film, 25K5, 0.1%, ±50ppm, 1/32W, 0201	MC004062	Resistor, Thin Film, 113R, 0.1%, ±25ppm, 1/32W, 0201	MC003573
Resistor, Thin Film, 1K07, 0.1%, ±50ppm, 1/32W, 0201	MC003908	Resistor, Thin Film, 1K58, 0.1%, ±25ppm, 1/32W, 0201	MC003701
Resistor, Thin Film, 365R, 0.1%, ±25ppm, 1/32W, 0201	MC003092	Resistor, Thin Film, 340R, 0.1%, ±25ppm, 1/32W, 0201	MC003626
Resistor, Thin Film, 3K24, 0.1%, ±25ppm, 1/32W, 0201	MC003198	Resistor, Thin Film, 3K92, 0.1%, ±25ppm, 1/32W, 0201	MC003747
Resistor, Thin Film, 4K32, 0.1%, ±50ppm, 1/32W, 0201	MC003976	Resistor, Thin Film, 57R6, 0.1%, ±50ppm, 1/32W, 0201	MC003765
Resistor, Thin Film, 150R, 0.1%, ±25ppm, 1/32W, 0201	MC003048	Resistor, Thin Film, 3K9, 0.1%, ±25ppm, 1/32W, 0201	MC003746
Resistor, Thin Film, 2K32, 0.1%, ±25ppm, 1/32W, 0201	MC003181	Resistor, Thin Film, 3K83, 0.1%, ±50ppm, 1/32W, 0201	MC003969
Resistor, Thin Film, 196R, 0.1%, ±50ppm, 1/32W, 0201	MC003285	Resistor, Thin Film, 1K33, 0.1%, ±25ppm, 1/32W, 0201	MC003156
Resistor, Thin Film, 68R, 0.1%, ±25ppm, 1/32W, 0201	MC003549	Resistor, Thin Film, 88R7, 0.1%, ±50ppm, 1/32W, 0201	MC003248
Resistor, Thin Film, 560R, 0.1%, ±25ppm, 1/32W, 0201	MC003652	Resistor, Thin Film, 1K15, 0.1%, ±50ppm, 1/32W, 0201	MC003373
Resistor, Thin Film, 681R, 0.1%, ±25ppm, 1/32W, 0201	MC003663	Resistor, Thin Film, 6K81, 0.1%, ±50ppm, 1/32W, 0201	MC003462
Resistor, Thin Film, 1K37, 0.1%, ±25ppm, 1/32W, 0201	MC003695	Resistor, Thin Film, 2K05, 0.1%, ±25ppm, 1/32W, 0201	MC003714



multicomp PRO

Description	Part Number	Description	Part Number
Resistor, Thin Film, 4K02, 0.1%, ±25ppm, 1/32W, 0201	MC003748	Resistor, Thin Film, 240R, 0.1%, ±50ppm, 1/32W, 0201	MC003294
Resistor, Thin Film, 2K55, 0.1%, ±25ppm, 1/32W, 0201	MC003186	Resistor, Thin Film, 390R, 0.1%, ±50ppm, 1/32W, 0201	MC003319
Resistor, Thin Film, 71R5, 0.1%, ±50ppm, 1/32W, 0201	MC003776	Resistor, Thin Film, 24K3, 0.1%, ±50ppm, 1/32W, 0201	MC003522
Resistor, Thin Film, 3K01, 0.1%, ±50ppm, 1/32W, 0201	MC003957	Resistor, Thin Film, 4K53, 0.1%, ±25ppm, 1/32W, 0201	MC003216
Resistor, Thin Film, 22K1, 0.1%, ±50ppm, 1/32W, 0201	MC004055	Resistor, Thin Film, 475R, 0.1%, ±50ppm, 1/32W, 0201	MC003330
Resistor, Thin Film, 2K15, 0.1%, ±50ppm, 1/32W, 0201	MC003940	Resistor, Thin Film, 680R, 0.1%, ±50ppm, 1/32W, 0201	MC003348
Resistor, Thin Film, 8K66, 0.1%, ±50ppm, 1/32W, 0201	MC004011	Resistor, Thin Film, 162R, 0.1%, ±25ppm, 1/32W, 0201	MC003590
Resistor, Thin Film, 56R2, 0.1%, ±25ppm, 1/32W, 0201	MC003002	Resistor, Thin Film, 2K1, 0.1%, ±25ppm, 1/32W, 0201	MC003715
Resistor, Thin Film, 174R, 0.1%, ±50ppm, 1/32W, 0201	MC003279	Resistor, Thin Film, 2K43, 0.1%, ±25ppm, 1/32W, 0201	MC003722
Resistor, Thin Film, 200R, 0.1%, ±50ppm, 1/32W, 0201	MC003286	Resistor, Thin Film, 69R8, 0.1%, ±50ppm, 1/32W, 0201	MC003775
Resistor, Thin Film, 383R, 0.1%, ±50ppm, 1/32W, 0201	MC003318	Resistor, Thin Film, 120R, 0.1%, ±50ppm, 1/32W, 0201	MC003800
Resistor, Thin Film, 475R, 0.1%, ±50ppm, 1/32W, 0201	MC003868	Resistor, Thin Film, 205R, 0.1%, ±50ppm, 1/32W, 0201	MC003825
Resistor, Thin Film, 120R, 0.1%, ±50ppm, 1/32W, 0201	MC003262	Resistor, Thin Film, 26K7, 0.1%, ±50ppm, 1/32W, 0201	MC004064
Resistor, Thin Film, 140R, 0.1%, ±50ppm, 1/32W, 0201	MC003269	Resistor, Thin Film, 187R, 0.1%, ±25ppm, 1/32W, 0201	MC003059
Resistor, Thin Film, 422R, 0.1%, ±50ppm, 1/32W, 0201	MC003861	Resistor, Thin Film, 422R, 0.1%, ±25ppm, 1/32W, 0201	MC003099
Resistor, Thin Film, 680R, 0.1%, ±50ppm, 1/32W, 0201	MC003886	Resistor, Thin Film, 2K61, 0.1%, ±25ppm, 1/32W, 0201	MC003187
Resistor, Thin Film, 4K3, 0.1%, ±50ppm, 1/32W, 0201	MC003975	Resistor, Thin Film, 162R, 0.1%, ±50ppm, 1/32W, 0201	MC003276
Resistor, Thin Film, 5K49, 0.1%, ±50ppm, 1/32W, 0201	MC003450	Resistor, Thin Film, 205R, 0.1%, ±50ppm, 1/32W, 0201	MC003287
Resistor, Thin Film, 51R, 0.1%, ±25ppm, 1/32W, 0201	MC003537	Resistor, Thin Film, 2K05, 0.1%, ±50ppm, 1/32W, 0201	MC003938
Resistor, Thin Film, 1K62, 0.1%, ±25ppm, 1/32W, 0201	MC003703	Resistor, Thin Film, 10K5, 0.1%, ±50ppm, 1/32W, 0201	MC004020
Resistor, Thin Film, 5K23, 0.1%, ±50ppm, 1/32W, 0201	MC003986	Resistor, Thin Film, 3K16, 0.1%, ±50ppm, 1/32W, 0201	MC003959
Resistor, Thin Film, 105R, 0.1%, ±25ppm, 1/32W, 0201	MC003032	Resistor, Thin Film, 240R, 0.1%, ±50ppm, 1/32W, 0201	MC003832
Resistor, Thin Film, 1K3, 0.1%, ±25ppm, 1/32W, 0201	MC003155	Resistor, Thin Film, 787R, 0.1%, ±50ppm, 1/32W, 0201	MC003893
Resistor, Thin Film, 280R, 0.1%, ±25ppm, 1/32W, 0201	MC003078	Resistor, Thin Film, 1K13, 0.1%, ±25ppm, 1/32W, 0201	MC003686
Resistor, Thin Film, 8K06, 0.1%, ±50ppm, 1/32W, 0201	MC003469	Resistor, Thin Film, 1K3, 0.1%, ±25ppm, 1/32W, 0201	MC003693
Resistor, Thin Film, 11K8, 0.1%, ±50ppm, 1/32W, 0201	MC003487	Resistor, Thin Film, 28K, 0.1%, ±50ppm, 1/32W, 0201	MC003529
Resistor, Thin Film, 2K49, 0.1%, ±50ppm, 1/32W, 0201	MC003409	Resistor, Thin Film, 93R1, 0.1%, ±25ppm, 1/32W, 0201	MC003565
Resistor, Thin Film, 3K, 0.1%, ±50ppm, 1/32W, 0201	MC003418	Resistor, Thin Film, 127R, 0.1%, ±25ppm, 1/32W, 0201	MC003579
Resistor, Thin Film, 5K23, 0.1%, ±50ppm, 1/32W, 0201	MC003448	Resistor, Thin Film, 510R, 0.1%, ±25ppm, 1/32W, 0201	MC003109
Resistor, Thin Film, 390R, 0.1%, ±25ppm, 1/32W, 0201	MC003633	Resistor, Thin Film, 140R, 0.1%, ±25ppm, 1/32W, 0201	MC003583
Resistor, Thin Film, 4K53, 0.1%, ±25ppm, 1/32W, 0201	MC003754	Resistor, Thin Film, 240R, 0.1%, ±25ppm, 1/32W, 0201	MC003608
Resistor, Thin Film, 1K54, 0.1%, ±25ppm, 1/32W, 0201	MC003162	Resistor, Thin Film, 102R, 0.1%, ±50ppm, 1/32W, 0201	MC003793
Resistor, Thin Film, 255R, 0.1%, ±50ppm, 1/32W, 0201	MC003835	Resistor, Thin Film, 1K05, 0.1%, ±50ppm, 1/32W, 0201	MC003907
Resistor, Thin Film, 13K, 0.1%, ±50ppm, 1/32W, 0201	MC004030	Resistor, Thin Film, 1K43, 0.1%, ±50ppm, 1/32W, 0201	MC003921
Resistor, Thin Film, 3K92, 0.1%, ±25ppm, 1/32W, 0201	MC003209	Resistor, Thin Film, 1K65, 0.1%, ±50ppm, 1/32W, 0201	MC003390
Resistor, Thin Film, 3K92, 0.1%, ±50ppm, 1/32W, 0201	MC003433	Resistor, Thin Film, 2K1, 0.1%, ±50ppm, 1/32W, 0201	MC003401
Resistor, Thin Film, 5K6, 0.1%, ±50ppm, 1/32W, 0201	MC003451	Resistor, Thin Film, 75R, 0.1%, ±25ppm, 1/32W, 0201	MC003554
Resistor, Thin Film, 110R, 0.1%, ±25ppm, 1/32W, 0201	MC003572	Resistor, Thin Film, 82R, 0.1%, ±50ppm, 1/32W, 0201	MC003782
Resistor, Thin Film, 66R5, 0.1%, ±25ppm, 1/32W, 0201	MC003548	Resistor, Thin Film, 90R9, 0.1%, ±25ppm, 1/32W, 0201	MC003025
Resistor, Thin Film, 1K02, 0.1%, ±50ppm, 1/32W, 0201	MC003906	Resistor, Thin Film, 324R, 0.1%, ±25ppm, 1/32W, 0201	MC003085
Resistor, Thin Film, 1K78, 0.1%, ±50ppm, 1/32W, 0201	MC003931	Resistor, Thin Film, 442R, 0.1%, ±25ppm, 1/32W, 0201	MC003102



multicomp PRO

Description	Part Number	Description	Part Number
Resistor, Thin Film, 620R, 0.1%, ±25ppm, 1/32W, 0201	MC003120	Resistor, Thin Film, 91R, 0.1%, ±25ppm, 1/32W, 0201	MC003026
Resistor, Thin Film, 66R5, 0.1%, ±50ppm, 1/32W, 0201	MC003234	Resistor, Thin Film, 511R, 0.1%, ±25ppm, 1/32W, 0201	MC003110
Resistor, Thin Film, 113R, 0.1%, ±50ppm, 1/32W, 0201	MC003259	Resistor, Thin Film, 820R, 0.1%, ±25ppm, 1/32W, 0201	MC003133
Resistor, Thin Film, 3K48, 0.1%, ±25ppm, 1/32W, 0201	MC003740	Resistor, Thin Film, 470R, 0.1%, ±50ppm, 1/32W, 0201	MC003329
Resistor, Thin Film, 66R5, 0.1%, ±50ppm, 1/32W, 0201	MC003772	Resistor, Thin Film, 165R, 0.1%, ±25ppm, 1/32W, 0201	MC003591
Resistor, Thin Film, 365R, 0.1%, ±50ppm, 1/32W, 0201	MC003854	Resistor, Thin Film, 392R, 0.1%, ±25ppm, 1/32W, 0201	MC003634
Resistor, Thin Film, 6K19, 0.1%, ±50ppm, 1/32W, 0201	MC003994	Resistor, Thin Film, 56R2, 0.1%, ±50ppm, 1/32W, 0201	MC003764
Resistor, Thin Film, 22K6, 0.1%, ±50ppm, 1/32W, 0201	MC004056	Resistor, Thin Film, 374R, 0.1%, ±50ppm, 1/32W, 0201	MC003855
Resistor, Thin Film, 665R, 0.1%, ±25ppm, 1/32W, 0201	MC003661	Resistor, Thin Film, 806R, 0.1%, ±50ppm, 1/32W, 0201	MC003894
Resistor, Thin Film, 178R, 0.1%, ±50ppm, 1/32W, 0201	MC003818	Resistor, Thin Film, 3K01, 0.1%, ±25ppm, 1/32W, 0201	MC003195
Resistor, Thin Film, 2K1, 0.1%, ±50ppm, 1/32W, 0201	MC003939	Resistor, Thin Film, 137R, 0.1%, ±50ppm, 1/32W, 0201	MC003268
Resistor, Thin Film, 909R, 0.1%, ±50ppm, 1/32W, 0201	MC003362	Resistor, Thin Film, 143R, 0.1%, ±50ppm, 1/32W, 0201	MC003270
Resistor, Thin Film, 590R, 0.1%, ±50ppm, 1/32W, 0201	MC003879	Resistor, Thin Film, 1K78, 0.1%, ±50ppm, 1/32W, 0201	MC003393
Resistor, Thin Film, 3K74, 0.1%, ±50ppm, 1/32W, 0201	MC003968	Resistor, Thin Film, 3K3, 0.1%, ±50ppm, 1/32W, 0201	MC003423
Resistor, Thin Film, 220R, 0.1%, ±25ppm, 1/32W, 0201	MC003066	Resistor, Thin Film, 1K1, 0.1%, ±25ppm, 1/32W, 0201	MC003685
Resistor, Thin Film, 3K48, 0.1%, ±50ppm, 1/32W, 0201	MC003426	Resistor, Thin Film, 210R, 0.1%, ±50ppm, 1/32W, 0201	MC003826
Resistor, Thin Film, 4K53, 0.1%, ±50ppm, 1/32W, 0201	MC003440	Resistor, Thin Film, 1K2, 0.1%, ±50ppm, 1/32W, 0201	MC003913
Resistor, Thin Film, 13K3, 0.1%, ±50ppm, 1/32W, 0201	MC004031	Resistor, Thin Film, 6K2, 0.1%, ±50ppm, 1/32W, 0201	MC003995
Resistor, Thin Film, 15K8, 0.1%, ±50ppm, 1/32W, 0201	MC004038	Resistor, Thin Film, 12K7, 0.1%, ±50ppm, 1/32W, 0201	MC004029
Resistor, Thin Film, 147R, 0.1%, ±25ppm, 1/32W, 0201	MC003047	Resistor, Thin Film, 86R6, 0.1%, ±25ppm, 1/32W, 0201	MC003023
Resistor, Thin Film, 160R, 0.1%, ±25ppm, 1/32W, 0201	MC003051	Resistor, Thin Film, 3K6, 0.1%, ±25ppm, 1/32W, 0201	MC003204
Resistor, Thin Film, 1K91, 0.1%, ±25ppm, 1/32W, 0201	MC003173	Resistor, Thin Film, 21K, 0.1%, ±50ppm, 1/32W, 0201	MC003514
Resistor, Thin Film, 64R9, 0.1%, ±25ppm, 1/32W, 0201	MC003547	Resistor, Thin Film, 182R, 0.1%, ±25ppm, 1/32W, 0201	MC003596
Resistor, Thin Film, 576R, 0.1%, ±25ppm, 1/32W, 0201	MC003654	Resistor, Thin Film, 383R, 0.1%, ±50ppm, 1/32W, 0201	MC003856
Resistor, Thin Film, 11K3, 0.1%, ±50ppm, 1/32W, 0201	MC004023	Resistor, Thin Film, 750R, 0.1%, ±50ppm, 1/32W, 0201	MC003891
Resistor, Thin Film, 19K6, 0.1%, ±50ppm, 1/32W, 0201	MC004049	Resistor, Thin Film, 232R, 0.1%, ±25ppm, 1/32W, 0201	MC003068
Resistor, Thin Film, 274R, 0.1%, ±50ppm, 1/32W, 0201	MC003301	Resistor, Thin Film, 249R, 0.1%, ±50ppm, 1/32W, 0201	MC003296
Resistor, Thin Film, 2K8, 0.1%, ±50ppm, 1/32W, 0201	MC003415	Resistor, Thin Film, 3K6, 0.1%, ±50ppm, 1/32W, 0201	MC003428
Resistor, Thin Film, 7K68, 0.1%, ±50ppm, 1/32W, 0201	MC004005	Resistor, Thin Film, 84R5, 0.1%, ±25ppm, 1/32W, 0201	MC003560
Resistor, Thin Film, 365R, 0.1%, ±25ppm, 1/32W, 0201	MC003630	Resistor, Thin Film, 121R, 0.1%, ±25ppm, 1/32W, 0201	MC003577
Resistor, Thin Film, 1K91, 0.1%, ±25ppm, 1/32W, 0201	MC003711	Resistor, Thin Film, 2K49, 0.1%, ±50ppm, 1/32W, 0201	MC003947
Resistor, Thin Film, 4K87, 0.1%, ±25ppm, 1/32W, 0201	MC003758	Resistor, Thin Film, 17K4, 0.1%, ±50ppm, 1/32W, 0201	MC004043
Resistor, Thin Film, 2K26, 0.1%, ±50ppm, 1/32W, 0201	MC003942	Resistor, Thin Film, 57R6, 0.1%, ±50ppm, 1/32W, 0201	MC003227
Resistor, Thin Film, 3K, 0.1%, ±50ppm, 1/32W, 0201	MC003956	Resistor, Thin Film, 6K2, 0.1%, ±50ppm, 1/32W, 0201	MC003457
Resistor, Thin Film, 715R, 0.1%, ±50ppm, 1/32W, 0201	MC003889	Resistor, Thin Film, 18K2, 0.1%, ±50ppm, 1/32W, 0201	MC003508
Resistor, Thin Film, 732R, 0.1%, ±50ppm, 1/32W, 0201	MC003890	Resistor, Thin Film, 210R, 0.1%, ±25ppm, 1/32W, 0201	MC003602
Resistor, Thin Film, 127R, 0.1%, ±50ppm, 1/32W, 0201	MC003265	Resistor, Thin Film, 220R, 0.1%, ±25ppm, 1/32W, 0201	MC003604
Resistor, Thin Film, 1K8, 0.1%, ±50ppm, 1/32W, 0201	MC003394	Resistor, Thin Film, 309R, 0.1%, ±25ppm, 1/32W, 0201	MC003621
Resistor, Thin Film, 61R9, 0.1%, ±25ppm, 1/32W, 0201	MC003544	Resistor, Thin Film, 3K24, 0.1%, ±25ppm, 1/32W, 0201	MC003736
Resistor, Thin Film, 261R, 0.1%, ±50ppm, 1/32W, 0201	MC003836	Resistor, Thin Film, 4K42, 0.1%, ±25ppm, 1/32W, 0201	MC003753
Resistor, Thin Film, 57R6, 0.1%, ±25ppm, 1/32W, 0201	MC003003	Resistor, Thin Film, 332R, 0.1%, ±50ppm, 1/32W, 0201	MC003849



multicomp PRO

Description	Part Number	Description	Part Number
Resistor, Thin Film, 866R, 0.1%, ±50ppm, 1/32W, 0201	MC003898	Resistor, Thin Film, 3K83, 0.1%, ±50ppm, 1/32W, 0201	MC003431
Resistor, Thin Film, 205R, 0.1%, ±25ppm, 1/32W, 0201	MC003063	Resistor, Thin Film, 25K5, 0.1%, ±50ppm, 1/32W, 0201	MC003524
Resistor, Thin Film, 1K96, 0.1%, ±25ppm, 1/32W, 0201	MC003174	Resistor, Thin Film, 115R, 0.1%, ±25ppm, 1/32W, 0201	MC003574
Resistor, Thin Film, 215R, 0.1%, ±50ppm, 1/32W, 0201	MC003289	Resistor, Thin Film, 806R, 0.1%, ±25ppm, 1/32W, 0201	MC003670
Resistor, Thin Film, 2K15, 0.1%, ±50ppm, 1/32W, 0201	MC003402	Resistor, Thin Film, 1K74, 0.1%, ±50ppm, 1/32W, 0201	MC003930
Resistor, Thin Film, 3K16, 0.1%, ±50ppm, 1/32W, 0201	MC003421	Resistor, Thin Film, 9K1, 0.1%, ±50ppm, 1/32W, 0201	MC004014
Resistor, Thin Film, 49R9, 0.1%, ±25ppm, 1/32W, 0201	MC003536	Resistor, Thin Film, 32K4, 0.1%, ±50ppm, 1/32W, 0201	MC004072
Resistor, Thin Film, 1K, 0.1%, ±25ppm, 1/32W, 0201	MC003681	Resistor, Thin Film, 430R, 0.1%, ±25ppm, 1/32W, 0201	MC003100
Resistor, Thin Film, 1K1, 0.1%, ±50ppm, 1/32W, 0201	MC003909	Resistor, Thin Film, 93R1, 0.1%, ±50ppm, 1/32W, 0201	MC003251
Resistor, Thin Film, 11K8, 0.1%, ±50ppm, 1/32W, 0201	MC004025	Resistor, Thin Film, 110R, 0.1%, ±50ppm, 1/32W, 0201	MC003258
Resistor, Thin Film, 121R, 0.1%, ±25ppm, 1/32W, 0201	MC003039	Resistor, Thin Film, 102R, 0.1%, ±25ppm, 1/32W, 0201	MC003031
Resistor, Thin Film, 127R, 0.1%, ±25ppm, 1/32W, 0201	MC003041	Resistor, Thin Film, 107R, 0.1%, ±25ppm, 1/32W, 0201	MC003033
Resistor, Thin Film, 3K48, 0.1%, ±50ppm, 1/32W, 0201	MC003964	Resistor, Thin Film, 2K2, 0.1%, ±25ppm, 1/32W, 0201	MC003179
Resistor, Thin Film, 16K9, 0.1%, ±50ppm, 1/32W, 0201	MC004042	Resistor, Thin Film, 2K67, 0.1%, ±25ppm, 1/32W, 0201	MC003188
Resistor, Thin Film, 453R, 0.1%, ±25ppm, 1/32W, 0201	MC003103	Resistor, Thin Film, 160R, 0.1%, ±50ppm, 1/32W, 0201	MC003275
Resistor, Thin Film, 348R, 0.1%, ±25ppm, 1/32W, 0201	MC003089	Resistor, Thin Film, 324R, 0.1%, ±50ppm, 1/32W, 0201	MC003309
Resistor, Thin Film, 806R, 0.1%, ±25ppm, 1/32W, 0201	MC003132	Resistor, Thin Film, 4K75, 0.1%, ±50ppm, 1/32W, 0201	MC003443
Resistor, Thin Film, 80R6, 0.1%, ±50ppm, 1/32W, 0201	MC003243	Resistor, Thin Film, 820R, 0.1%, ±25ppm, 1/32W, 0201	MC003671
Resistor, Thin Film, 8K25, 0.1%, ±50ppm, 1/32W, 0201	MC003471	Resistor, Thin Film, 68R1, 0.1%, ±50ppm, 1/32W, 0201	MC003774
Resistor, Thin Film, 887R, 0.1%, ±50ppm, 1/32W, 0201	MC003899	Resistor, Thin Film, 121R, 0.1%, ±50ppm, 1/32W, 0201	MC003801
Resistor, Thin Film, 82R5, 0.1%, ±25ppm, 1/32W, 0201	MC003021	Resistor, Thin Film, 137R, 0.1%, ±25ppm, 1/32W, 0201	MC003044
Resistor, Thin Film, 1K47, 0.1%, ±25ppm, 1/32W, 0201	MC003160	Resistor, Thin Film, 62R, 0.1%, ±25ppm, 1/32W, 0201	MC003007
Resistor, Thin Film, 2K1, 0.1%, ±25ppm, 1/32W, 0201	MC003177	Resistor, Thin Film, 442R, 0.1%, ±25ppm, 1/32W, 0201	MC003640
Resistor, Thin Film, 2K74, 0.1%, ±25ppm, 1/32W, 0201	MC003190	Resistor, Thin Film, 2K8, 0.1%, ±25ppm, 1/32W, 0201	MC003729
Resistor, Thin Film, 154R, 0.1%, ±50ppm, 1/32W, 0201	MC003273	Resistor, Thin Film, 4K87, 0.1%, ±50ppm, 1/32W, 0201	MC003982
Resistor, Thin Film, 2K2, 0.1%, ±50ppm, 1/32W, 0201	MC003403	Resistor, Thin Film, 76R8, 0.1%, ±25ppm, 1/32W, 0201	MC003017
Resistor, Thin Film, 4K12, 0.1%, ±50ppm, 1/32W, 0201	MC003435	Resistor, Thin Film, 887R, 0.1%, ±25ppm, 1/32W, 0201	MC003137
Resistor, Thin Film, 4K42, 0.1%, ±50ppm, 1/32W, 0201	MC003439	Resistor, Thin Film, 1K02, 0.1%, ±25ppm, 1/32W, 0201	MC003144
Resistor, Thin Film, 33K, 0.1%, ±50ppm, 1/32W, 0201	MC003535	Resistor, Thin Film, 1K13, 0.1%, ±25ppm, 1/32W, 0201	MC003148
Resistor, Thin Film, 1K07, 0.1%, ±25ppm, 1/32W, 0201	MC003684	Resistor, Thin Film, 340R, 0.1%, ±50ppm, 1/32W, 0201	MC003312
Resistor, Thin Film, 75R, 0.1%, ±50ppm, 1/32W, 0201	MC003778	Resistor, Thin Film, 2K43, 0.1%, ±50ppm, 1/32W, 0201	MC003408
Resistor, Thin Film, 78R7, 0.1%, ±50ppm, 1/32W, 0201	MC003780	Resistor, Thin Film, 140R, 0.1%, ±50ppm, 1/32W, 0201	MC003807
Resistor, Thin Film, 226R, 0.1%, ±50ppm, 1/32W, 0201	MC003829	Resistor, Thin Film, 1K8, 0.1%, ±50ppm, 1/32W, 0201	MC003932
Resistor, Thin Film, 2K94, 0.1%, ±50ppm, 1/32W, 0201	MC003955	Resistor, Thin Film, 8K87, 0.1%, ±50ppm, 1/32W, 0201	MC004012
Resistor, Thin Film, 604R, 0.1%, ±25ppm, 1/32W, 0201	MC003118	Resistor, Thin Film, 10K2, 0.1%, ±50ppm, 1/32W, 0201	MC004019
Resistor, Thin Film, 562R, 0.1%, ±50ppm, 1/32W, 0201	MC003339	Resistor, Thin Film, 3K3, 0.1%, ±25ppm, 1/32W, 0201	MC003199
Resistor, Thin Film, 649R, 0.1%, ±50ppm, 1/32W, 0201	MC003346	Resistor, Thin Film, 487R, 0.1%, ±50ppm, 1/32W, 0201	MC003331
Resistor, Thin Film, 750R, 0.1%, ±50ppm, 1/32W, 0201	MC003353	Resistor, Thin Film, 7K87, 0.1%, ±50ppm, 1/32W, 0201	MC003468
Resistor, Thin Film, 357R, 0.1%, ±50ppm, 1/32W, 0201	MC003852	Resistor, Thin Film, 14K, 0.1%, ±50ppm, 1/32W, 0201	MC003495
Resistor, Thin Film, 5K1, 0.1%, ±50ppm, 1/32W, 0201	MC003984	Resistor, Thin Film, 332R, 0.1%, ±25ppm, 1/32W, 0201	MC003625
Resistor, Thin Film, 3K32, 0.1%, ±50ppm, 1/32W, 0201	MC003424	Resistor, Thin Film, 2K4, 0.1%, ±25ppm, 1/32W, 0201	MC003721



multicomp PRO

Description	Part Number	Description	Part Number
Resistor, Thin Film, 5K11, 0.1%, ±50ppm, 1/32W, 0201	MC003985	Resistor, Thin Film, 309R, 0.1%, ±50ppm, 1/32W, 0201	MC003307
Resistor, Thin Film, 24K9, 0.1%, ±50ppm, 1/32W, 0201	MC003523	Resistor, Thin Film, 102R, 0.1%, ±25ppm, 1/32W, 0201	MC003569
Resistor, Thin Film, 1K4, 0.1%, ±25ppm, 1/32W, 0201	MC003696	Resistor, Thin Film, 1K13, 0.1%, ±50ppm, 1/32W, 0201	MC003910
Resistor, Thin Film, 15K4, 0.1%, ±50ppm, 1/32W, 0201	MC004037	Resistor, Thin Film, 5K62, 0.1%, ±50ppm, 1/32W, 0201	MC003990
Resistor, Thin Film, 19K1, 0.1%, ±50ppm, 1/32W, 0201	MC004048	Resistor, Thin Film, 21K5, 0.1%, ±50ppm, 1/32W, 0201	MC004053
Resistor, Thin Film, 180R, 0.1%, ±25ppm, 1/32W, 0201	MC003057	Resistor, Thin Film, 63R4, 0.1%, ±50ppm, 1/32W, 0201	MC003232
Resistor, Thin Film, 681R, 0.1%, ±50ppm, 1/32W, 0201	MC003349	Resistor, Thin Film, 931R, 0.1%, ±50ppm, 1/32W, 0201	MC003364
Resistor, Thin Film, 10K5, 0.1%, ±50ppm, 1/32W, 0201	MC003482	Resistor, Thin Film, 9K53, 0.1%, ±50ppm, 1/32W, 0201	MC003478
Resistor, Thin Film, 374R, 0.1%, ±25ppm, 1/32W, 0201	MC003631	Resistor, Thin Film, 11K3, 0.1%, ±50ppm, 1/32W, 0201	MC003485
Resistor, Thin Film, 3K6, 0.1%, ±25ppm, 1/32W, 0201	MC003742	Resistor, Thin Film, 249R, 0.1%, ±25ppm, 1/32W, 0201	MC003610
Resistor, Thin Film, 3K9, 0.1%, ±50ppm, 1/32W, 0201	MC003970	Resistor, Thin Film, 3K32, 0.1%, ±25ppm, 1/32W, 0201	MC003738
Resistor, Thin Film, 5K36, 0.1%, ±50ppm, 1/32W, 0201	MC003987	Resistor, Thin Film, 309R, 0.1%, ±50ppm, 1/32W, 0201	MC003845
Resistor, Thin Film, 1K74, 0.1%, ±25ppm, 1/32W, 0201	MC003168	Resistor, Thin Film, 820R, 0.1%, ±50ppm, 1/32W, 0201	MC003895
Resistor, Thin Film, 2K49, 0.1%, ±25ppm, 1/32W, 0201	MC003185	Resistor, Thin Film, 154R, 0.1%, ±25ppm, 1/32W, 0201	MC003049
Resistor, Thin Film, 1K87, 0.1%, ±50ppm, 1/32W, 0201	MC003396	Resistor, Thin Film, 1K07, 0.1%, ±25ppm, 1/32W, 0201	MC003146
Resistor, Thin Film, 590R, 0.1%, ±25ppm, 1/32W, 0201	MC003655	Resistor, Thin Film, 2K15, 0.1%, ±25ppm, 1/32W, 0201	MC003178
Resistor, Thin Film, 137R, 0.1%, ±50ppm, 1/32W, 0201	MC003806	Resistor, Thin Film, 133R, 0.1%, ±50ppm, 1/32W, 0201	MC003267
Resistor, Thin Film, 931R, 0.1%, ±50ppm, 1/32W, 0201	MC003902	Resistor, Thin Film, 1K74, 0.1%, ±50ppm, 1/32W, 0201	MC003392
Resistor, Thin Film, 1K87, 0.1%, ±50ppm, 1/32W, 0201	MC003934	Resistor, Thin Film, 5K36, 0.1%, ±50ppm, 1/32W, 0201	MC003449
Resistor, Thin Film, 3K3, 0.1%, ±50ppm, 1/32W, 0201	MC003961	Resistor, Thin Film, 62R, 0.1%, ±25ppm, 1/32W, 0201	MC003545
Resistor, Thin Film, 124R, 0.1%, ±25ppm, 1/32W, 0201	MC003040	Resistor, Thin Film, 105R, 0.1%, ±25ppm, 1/32W, 0201	MC003570
Resistor, Thin Film, 255R, 0.1%, ±25ppm, 1/32W, 0201	MC003073	Resistor, Thin Film, 133R, 0.1%, ±25ppm, 1/32W, 0201	MC003581
Resistor, Thin Film, 4K02, 0.1%, ±25ppm, 1/32W, 0201	MC003210	Resistor, Thin Film, 1K18, 0.1%, ±25ppm, 1/32W, 0201	MC003688
Resistor, Thin Film, 820R, 0.1%, ±50ppm, 1/32W, 0201	MC003357	Resistor, Thin Film, 249R, 0.1%, ±50ppm, 1/32W, 0201	MC003834
Resistor, Thin Film, 3K09, 0.1%, ±25ppm, 1/32W, 0201	MC003734	Resistor, Thin Film, 3K09, 0.1%, ±50ppm, 1/32W, 0201	MC003958
Resistor, Thin Film, 63R4, 0.1%, ±50ppm, 1/32W, 0201	MC003770	Resistor, Thin Film, 182R, 0.1%, ±25ppm, 1/32W, 0201	MC003058
Resistor, Thin Film, 2K05, 0.1%, ±25ppm, 1/32W, 0201	MC003176	Resistor, Thin Film, 61R9, 0.1%, ±25ppm, 1/32W, 0201	MC003006
Resistor, Thin Film, 301R, 0.1%, ±50ppm, 1/32W, 0201	MC003306	Resistor, Thin Film, 9K31, 0.1%, ±50ppm, 1/32W, 0201	MC003477
Resistor, Thin Film, 73R2, 0.1%, ±25ppm, 1/32W, 0201	MC003553	Resistor, Thin Film, 19K6, 0.1%, ±50ppm, 1/32W, 0201	MC003511
Resistor, Thin Film, 1K47, 0.1%, ±25ppm, 1/32W, 0201	MC003698	Resistor, Thin Film, 4K22, 0.1%, ±50ppm, 1/32W, 0201	MC003974
Resistor, Thin Film, 160R, 0.1%, ±50ppm, 1/32W, 0201	MC003813	Resistor, Thin Film, 1K05, 0.1%, ±25ppm, 1/32W, 0201	MC003145
Resistor, Thin Film, 5K76, 0.1%, ±50ppm, 1/32W, 0201	MC003991	Resistor, Thin Film, 191R, 0.1%, ±50ppm, 1/32W, 0201	MC003284
Resistor, Thin Film, 20K, 0.1%, ±50ppm, 1/32W, 0201	MC004050	Resistor, Thin Film, 4K64, 0.1%, ±50ppm, 1/32W, 0201	MC003441
Resistor, Thin Film, 21K, 0.1%, ±50ppm, 1/32W, 0201	MC004052	Resistor, Thin Film, 118R, 0.1%, ±50ppm, 1/32W, 0201	MC003799
Resistor, Thin Film, 549R, 0.1%, ±25ppm, 1/32W, 0201	MC003113	Resistor, Thin Film, 243R, 0.1%, ±50ppm, 1/32W, 0201	MC003833
Resistor, Thin Film, 8K66, 0.1%, ±50ppm, 1/32W, 0201	MC003473	Resistor, Thin Film, 11K, 0.1%, ±50ppm, 1/32W, 0201	MC004022
Resistor, Thin Film, 12K4, 0.1%, ±50ppm, 1/32W, 0201	MC003490	Resistor, Thin Film, 13K7, 0.1%, ±50ppm, 1/32W, 0201	MC004032
Resistor, Thin Film, 4K22, 0.1%, ±25ppm, 1/32W, 0201	MC003750	Resistor, Thin Film, 97R6, 0.1%, ±25ppm, 1/32W, 0201	MC003029
Resistor, Thin Film, 330R, 0.1%, ±50ppm, 1/32W, 0201	MC003848	Resistor, Thin Film, 51R, 0.1%, ±50ppm, 1/32W, 0201	MC003223
Resistor, Thin Film, 4K7, 0.1%, ±50ppm, 1/32W, 0201	MC003980	Resistor, Thin Film, 9K1, 0.1%, ±50ppm, 1/32W, 0201	MC003476
Resistor, Thin Film, 220R, 0.1%, ±50ppm, 1/32W, 0201	MC003290	Resistor, Thin Film, 13K7, 0.1%, ±50ppm, 1/32W, 0201	MC003494



multicomp PRO

Description	Part Number	Description	Part Number
Resistor, Thin Film, 205R, 0.1%, ±25ppm, 1/32W, 0201	MC003601	Resistor, Thin Film, 953R, 0.1%, ±25ppm, 1/32W, 0201	MC003679
Resistor, Thin Film, 274R, 0.1%, ±25ppm, 1/32W, 0201	MC003615	Resistor, Thin Film, 1K65, 0.1%, ±25ppm, 1/32W, 0201	MC003704
Resistor, Thin Film, 300R, 0.1%, ±50ppm, 1/32W, 0201	MC003843	Resistor, Thin Film, 1K21, 0.1%, ±50ppm, 1/32W, 0201	MC003914
Resistor, Thin Film, 2K26, 0.1%, ±25ppm, 1/32W, 0201	MC003180	Resistor, Thin Film, 2K61, 0.1%, ±50ppm, 1/32W, 0201	MC003949
Resistor, Thin Film, 56R2, 0.1%, ±25ppm, 1/32W, 0201	MC003540	Resistor, Thin Film, 3K24, 0.1%, ±50ppm, 1/32W, 0201	MC003960
Resistor, Thin Film, 768R, 0.1%, ±25ppm, 1/32W, 0201	MC003668	Resistor, Thin Film, 26K1, 0.1%, ±50ppm, 1/32W, 0201	MC004063

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

