
Surface-mounted luminaire





ENGINEER OF LIGHT.

Energy efficiency category A+



fitted with LED

work equipment without
connected load 18-30 V; DC
power consumption approx. 18 W
luminous flux approx. 1350 lm
luminous efficacy approx. 75 lm/W

light distribution direct

Beam Angle C0-C180: 80° / C90-C270: 100° light colour neutral white, approx. 5000 K

 color rendering index (CRI)
 > 80

 system of protection
 IP 67

 class of protection
 III

 technology
 switchable

 usage
 external

luminaire body aluminium, anodised, aluminium coloured anodised

lamp coverscreen, clearweight (net)approx. 1.9 kgmains supplybuilt-in plugSerie_763

designmounted versionfasteningL-angle, clampdimensionA=565 mmspecial featuresPower equipment





Serie_763

illuminance

luminous intensity

