


Deep groove ball bearings, single row, seal on both sides

Principal dimensions			Basic load ratings		Fatigue load limit P_u	Speed ratings		Mass	Designation
d	D	B	dynamic	static		Reference speed	Limiting speed		
mm			kN		kN	r/min		kg	* - SKF Explorer bearing
12	37	12	10,1	4,15	0,176	-	14000	0,060	6301-2RSH *



Calculation factors

k_r 0,03

f_0 11