



### Connection Products

#### Nylon Cable Glands

Nylon domed headed cable glands are quick and easy to install and cater for a wide range of cable sizes.

A range of quality nylon cable glands that can be used on a wide range of applications when connecting cable to electrical equipment (but not steel wire armoured cable).

#### Features and Benefits

- Material Nylon 66
- Low smoke, zero halogen
- IP rating IP68
- Metric thread
- Available in red, black, white, dark grey and grey
- Euro slot packaging
- Complete with lock nut and washer



Nylon Cable Glands.

TYPE	Size	Colour	Cable Clamp Range	Pack Cont.
NGM12RD	M12	Red (RD)	3-6.5mm	10
NGM12WE	M12	White (WE)	3-6.5mm	10
NGM12GY	M12	Grey (GY)	3-6.5mm	10
NGM12DGY	M12	Dark Grey (DGY)	3-6.5mm	10
NGM12BK	M12	Black (BK)	3-6.5mm	10
NGM16RD	M16	Red (RD)	5-10mm	10
NGM16WE	M16	White (WE)	5-10mm	10
NGM16GY	M16	Grey (GY)	5-10mm	10
NGM16DGY	M16	Dark Grey (DGY)	5-10mm	10
NGM16BK	M16	Black (BK)	5-10mm	10
NGM20SRD	M20	Red (RD)	6-12mm	10
NGM20SWE	M20	White (WE)	6-12mm	10
NGM20SGY	M20	Grey (GY)	6-12mm	10
NGM20SDGY	M20	Dark Grey (DGY)	6-12mm	10
NGM20SBK	M20	Black (BK)	6-12mm	10
NGM20RD	M20	Red (RD)	10-14mm	10
NGM20WE	M20	White (WE)	10-14mm	10
NGM20GY	M20	Grey (GY)	10-14mm	10
NGM20DGY	M20	Dark Grey (DGY)	10-14mm	10
NGM20BK	M20	Black (BK)	10-14mm	10
NGM25RD	M25	Red (RD)	13-18mm	10
NGM25WE	M25	White (WE)	13-18mm	10
NGM25GY	M25	Grey (GY)	13-18mm	10
NGM25DGY	M25	Dark Grey (DGY)	13-18mm	10
NGM25BK	M25	Black (BK)	13-18mm	10
NGM32RD	M32	Red (RD)	18-25mm	5
NGM32WE	M32	White (WE)	18-25mm	5
NGM32GY	M32	Grey (GY)	18-25mm	5
NGM32DGY	M32	Dark Grey (DGY)	18-25mm	5
NGM32BK	M32	Black (BK)	18-25mm	5
NGM40RD	M40	Red (RD)	22-32mm	5
NGM40WE	M40	White (WE)	22-32mm	5
NGM40GY	M40	Grey (GY)	22-32mm	5
NGM40DGY	M40	Dark Grey (DGY)	22-32mm	5
NGM40BK	M40	Black (BK)	22-32mm	5
NGM50RD	M50	Red (RD)	30-38mm	2
NGM50WE	M50	White (WE)	30-38mm	2
NGM50GY	M50	Grey (GY)	30-38mm	2
NGM50DGY	M50	Dark Grey (DGY)	30-38mm	2
NGM50BK	M50	Black (BK)	30-38mm	2
NGM63RD	M63	Red (RD)	34-44mm	2
NGM63WE	M63	White (WE)	34-44mm	2
NGM63GY	M63	Grey (GY)	34-44mm	2
NGM63DGY	M63	Dark Grey (DGY)	34-44mm	2
NGM63BK	M63	Black (BK)	34-44mm	2



Other colours available on request subject to minimum order quantity and lead times