

SOLID PC 3819 13 T



Sample photo

Order symbol: PC 3819 13 T
Product nbr: 5330061
Description: Enclosure, PC
Remarks: Transparent cover

EAN: 6418074005472
EI. number:
 Finland: 3423809
 Electric No. Italy: 7402030
 Electric No. Sweden: 2539444

Including: Base with screws for mounting plate, cover with PUR gasket and polyamide cover screws.

Dimensions:				Accessories:	
	Length	Width	Height		
mm:	378	188	130	EKMXT	Mounting plate isolated
inch:	14.9	7.4	5.1	EKV 12	DIN-35 Mounting rail
				EKV 32	DIN-35 Mounting rail
				EKMZR	Extension frame
Materials:				Rating:	
Material:	Polycarbonate			Ingress Protection (EN 60529): IP66/IP67	
Base colour:	RAL 7035 -light grey			Impact Resistance (EN 62262): IK08/IK09	
Cover screws material:	Polyamide			Electrical insulation: Totally insulated	
Cover colour:	Clear transparent			Halogen free (DIN/VDE 0472, Part 815): 1	
Cover screws colour:	Grey			UV resistance: UL 508	
Gasket material:	Polyurethane			Flammability Rating: UL 746C 5"	
				Glow Wire Test (IEC 695-2-1) °C: 960	
				NEMA Class: NEMA 1, 3, 3S, 4, 4X, 6, 6P, 12	
Temperatures:				Certificates:	
Temperature °C (short term):	-40 ... 120 °C			SGS Fimko	
Temperature °C (continuous):	-40 ... 80 °C			Gost R	
Temperature °F (short term):	-40 ... 250 °F				
Temperature °F (continuous):	-40 ... 175 °F				
Accessories:					
EKMVT	Mounting plate				

