

# Technical data sheet

## Cable/pipe fastening systems, metal



Type	Clamping range D mm	Bolt	Pack. pcs	Weight kg/100 pcs.	Item No.
ASL 733 10 G	8-10	–	25	1,794	1362754
ASL 733 12 G	10-12	–	25	1,857	1362756
ASL 733 14 G	12-14	–	25	1,936	1362758
ASL 733 17 G	14-17	–	25	2,099	1362762
ASL 733 20 G	17-20	–	25	2,201	1362764
ASL 733 25 G	20-25	–	25	2,419	1362768
ASL 733 30 G	25-30	–	20	3,401	1362772
ASL 733 36 G	30-36	–	20	3,774	1362776
ASL 733 44 G	36-44	–	20	4,151	1362780
ASL 733 53 G	44-53	–	20	5,616	1362784
ASL 733 63 G	53-63	–	20	6,212	1362788
ASL 733 10 FT	8-10	–	25	1,883	1362704
ASL 733 12 FT	10-12	–	25	1,951	1362706
ASL 733 14 FT	12-14	–	25	2,035	1362708
ASL 733 17 FT	14-17	–	25	2,206	1362712
ASL 733 20 FT	17-20	–	25	2,315	1362714
ASL 733 25 FT	20-25	–	25	2,540	1362718
ASL 733 30 FT	25-30	–	20	3,567	1362722
ASL 733 36 FT	30-36	–	20	3,956	1362726
ASL 733 44 FT	36-44	–	20	4,356	1362730
ASL 733 53 FT	44-53	–	20	5,850	1362734
ASL 733 63 FT	53-63	–	20	6,477	1362738

**G** Electrogalvanised

**FT** Hot-dip galvanised

### Dimensions

