
# Product datasheet Characteristics

## NSYMR33

Monobloc perforated plates H300xW300mm with universal perforations 11x26mm



Price\*: 9.91 GBP



### Main

Range Spacial  Accessory / separate part category Mounting accessory	
Accessory / separate part category Mounting accessory	
Accessory / separate part category woodniting accessory	
Product or component type Mounting plate	<u> </u>
Application Multi-purpose	<u></u>
For enclosure nominal dimensions 300 mm W: 300 mm	<u>ii</u>
Mounting location Step slide Direct fixing on backstuds	
Mounting plate description Telequick perforated	
Range compatibility Spacial CRN Spacial S3D Spacial S3X Thalassa PLM	for determining
Quantity per set Set of 1	
Material Steel	
Surface finish Zinc coated	.0

### Complementary

- Complementary		
Fixing mode	Screwed on backstuds - screw type M8 By fixing element	
Height	255 mm	
Width	251 mm	
Depth	15 mm	
Thickness	2 mm	
Product weight	0.506 kg	
Number of slots	144	
Variant particularity	Installation in rear of enclosure	
Cut-out dimensions	11 x 26 mm	

### Offer Sustainability

Sustainable offer status	Green Premium product	
RoHS (date code: YYWW)	Compliant - since 0940 - Schneider Electric declaration of conformity	
	Schneider Electric declaration of conformity	
REACh	Reference not containing SVHC above the threshold	
	Reference not containing SVHC above the threshold	
Product environmental profile	Available	
	Product Environmental Profile	
Product end of life instructions	Need no specific recycling operations	

Warranty period	18 months	