

PSS-08-01-T-S PSS-13-01-T-S **PSS SERIES**

(5.08 mm) .200"

POWER SOCKET STRIP

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com?PSS

Insulator Material: Black LCP Contact Material:

BeCu

Plating:

Sn over 50 µ" (1.27 µm) Ni Current Rating (PSS/FWS): 11.4 A per pin

(1 pin powered) Insertion Depth: (2.62 mm) .103" to (5.03 mm) .198"

Voltage Rating: 500 VAC mated with FWS RoHS Compliant:

PROCESSING

Lead-Free Solderable:


SMT Lead Coplanarity: (0.15 mm) .006" max (02-14)* (0.20 mm) .008" max (15-20)* *(.004" stencil solution may be available; contact IPG@samtec.com)


RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality



Mates with: FWS, HFWS, SW, HPM, HPW





Some lengths, styles and options are non-standard, non-returnable.