


Machined Type Needle Roller Bearings

(R)NA49 | (R)NA49UU | (R)NA69 | (R)NA69UU | (R)NA48 | (R)NAF
TAF(I) | TR(I) | BR | GBR | GBRUU | LRB | NAG49..(UU)

Machined Type Needle Roller Bearings TAFI



IKONumber with inner race TAFI	IKONumber without inner race TAF	Dimensions (mm)			
		d	dr	D	B
-	TAF-71410	-	7	14	10
-	TAF-71412	-	7	14	12
TAFI-51512	TAF-81512	5	8	15	12
TAFI-51516	TAF-81516	5	8	15	16
TAFI-61612	TAF-91612	6	9	16	12
TAFI-61616	TAF-91616	6	9	16	16
TAFI-71712	TAF-101712	7	10	17	12
TAFI-71716	TAF-101716	7	10	17	16
TAFI-91912	TAF-121912	9	12	19	12
TAFI-91916	TAF-121916	9	12	19	16
TAFI-102216	TAF-142216	10	14	22	16
TAFI-102220	TAF-142220	10	14	22	20
-	TAF-152316	-	15	23	16
-	TAF-152320	-	15	23	20
TAFI-122416	TAF-162416	12	16	24	16
TAFI-122420	TAF-162420	12	16	24	20
-	TAF-172516	-	17	25	16
-	TAF-172520	-	17	25	20
-	TAF-182616	-	18	26	16
-	TAF-182620	-	18	26	20
TAFI-152716	TAF-192716	15	19	27	16
TAFI-152720	TAF-192720	15	19	27	20
-	TAF-202816	-	20	28	16
-	TAF-202820	-	20	28	20

IKONumber with inner race TAFI	IKONumber without inner race TAF	Dimensions (mm)			
		d	dr	D	B
TAFI-172916	TAF-212916	17	21	29	16
TAFI-172920	TAF-212920	17	21	29	20
-	TAF-223016	-	22	30	16
-	TAF-223020	-	22	30	20
TAFI-203216	TAF-243216	20	24	32	16
TAFI-203220	TAF-243220	20	24	32	20
-	TAF-253316	-	25	33	16
-	TAF-253320	-	25	33	20
TAFI-223416	TAF-263416	22	26	34	16
TAFI-223420	TAF-263420	22	26	34	20
-	TAF-283720	-	28	37	20
-	TAF-283730	-	28	37	30
TAFI-253820	TAF-293820	25	29	38	20
TAFI-253830	TAF-293830	25	29	38	30
-	TAF-304020	-	30	40	20
-	TAF-304030	-	30	40	30
TAFI-284220	TAF-324220	28	32	42	20

TAFI-284230	TAF-324230	28	32	42	30
TAFI-304520	TAF-354520	30	35	45	20
TAFI-304530	TAF-354530	30	35	45	30
TAFI-324720	TAF-374720	32	37	47	20
TAFI-324730	TAF-374730	32	37	47	30
-	TAF-384820	-	38	48	20
-	TAF-384830	-	38	48	30
TAFI-355020	TAF-405020	35	40	50	20
TAFI-355030	TAF-405030	35	40	50	30
-	TAF-425220	-	42	52	20
-	TAF-425230	-	42	52	30
TAFI-385320	TAF-435320	38	43	53	20
TAFI-385330	TAF-435330	38	43	53	30
TAFI-405520	TAF-455520	40	45	55	20
TAFI-405530	TAF-455530	40	45	55	30
TAFI-425720	TAF-475720	42	47	57	20

IKONumber with inner race TAFI	IKONumber without inner race TAF	Dimensions (mm)			
		d	dr	D	B
TAFI-425730	TAF-475730	42	47	57	30
TAFI-456225	TAF-506225	45	50	62	25
TAFI-456235	TAF-506235	45	50	62	35
TAFI-506825	TAF-556825	50	55	68	25
TAFI-506835	TAF-556835	50	55	68	35
TAFI-557225	TAF-607225	55	60	72	25
TAFI-557235	TAF-607235	55	60	72	35
-	TAF-657825	-	65	78	25
-	TAF-657835	-	65	78	35
TAFI-608225	TAF-688225	60	68	82	25
TAFI-608235	TAF-688235	60	68	82	35
-	TAF-708525	-	70	85	25
-	TAF-708535	-	70	85	35
-	TAF-739025	-	73	90	25
TAFI-659035	TAF-739035	65	73	90	35
-	TAF-759225	-	75	92	25
-	TAF-759235	-	75	92	35
TAFI-709525	TAF-809525	70	80	95	25
TAFI-709535	TAF-809535	70	80	95	35
TAFI-7510525	TAF-8510525	75	85	105	25
TAFI-7510535	TAF-8510535	75	85	105	35
TAFI-8011025	TAF-9011025	80	90	110	25
TAFI-8011035	TAF-9011035	80	90	110	35
TAFI-8511526	TAF-9511526	85	95	115	26
TAFI-8511536	TAF-9511536	85	95	115	36
TAFI-9012026	TAF-10012026	90	100	120	26
TAFI-9012036	TAF-10012036	90	100	120	36
TAFI-9512526	TAF-10512526	95	105	125	26
TAFI-9512536	TAF-10512536	95	105	125	36
TAFI-10013030	TAF-11013030	100	110	130	30
TAFI-10013040	TAF-11013040	100	110	130	40
