



NEU  
NEW



## Product information

### Mobile LED Light JARO 3003 M, 2930lm, 30W, IP65 \*GB\*

#### For indoor and outdoor use, IP 65.

- LED Light with extra bright Everlight SMD LEDs.
  - Solid and modern aluminium casing.
  - Stable steel tube frame with plastic corner protectors and ergonomically formed plastic carrier handle.
  - Steplessly pivotable light which can be locked with one hand by means of a quick-release fastener.
  - With safety glass.
  - In colourful display-packaging.
  - This luminaire contains built-in LED lamps.
  - Light unit not replaceable.
- Scope of delivery: 1x JARO 3003 M LED floodlight with 3m cable and BS 1363 plug - in best brennenstuhl® quality

## Technical information

|                                       |               |
|---------------------------------------|---------------|
| Product number                        | 1171253343    |
| EAN-Code                              | 4007123656059 |
| UP                                    | 1             |
| Total luminous flux                   | 2930 lm       |
| Power                                 | 30 W          |
| Efficacy                              | 95 lm/W       |
| Energy efficiency class               | A+            |
| Nominal input voltage                 | 230 V         |
| Max. nominal input voltage            | 240 V         |
| Cable length                          | 3 m           |
| Cable designation                     | H07RN-F 3G1,0 |
| Degree of protection (IP)             | IP65          |
| Protection class                      | I             |
| Colour                                | black, Yellow |
| Fittings                              | Without       |
| Weight of product (without packaging) | 2,36 kg       |
| Length of product (without packaging) | 30,35 cm      |
| Width of product (without packaging)  | 16,30 cm      |
| Height of product (without packaging) | 28,95 cm      |

|                                         |          |
|-----------------------------------------|----------|
| Weight of product (including packaging) | 2,50 kg  |
| Length of product (including packaging) | 32,20 cm |
| Width of product (including packaging)  | 17,50 cm |
| Height of product (including packaging) | 31,50 cm |