




Speaker Specification



Customer's Model No.		Customer		componet	
Kepo Model No.		KPSP50105PF-32/0.5G	Size	Φ 50mm	No. J24423
No.	Item	Specification	Test Condition		
1	Impedance	32Ω± 15%	at 800Hz		
2	Resonant Fr. (f ₀)	600Hz± 20%			
3	Frequency Range	F0-6KHz			
4	Rated Power	0.5W			
5	Max Power	0.6W			
6	S.P.L.	88± 3dB	0.1W / 0.1M at 0.8,1,1.2,1.5kHz AVG		
7	Distortion	Max 5%	at rated power 1.0kHz		
8	Sweep Test	must be normal	at sine wave 1.41V		
9	Load Test	after test meet item 8	rated noise power, 24 Hrs.		
10	Heat Test	after test meet item 8	50± 2℃ 5Hrs.		
11	Cold Test	after test meet item 8	-25± 2℃ 5Hrs.		
12	Humidity Test	after test meet item 8	40± 2℃,90/95%R.H. 5Hrs.		
13	Weight				
14	Polarity Test	When supplied plus D.C. voltage to (+) terminal, the cone must move to forward.			
15	Note				



Dimensions:



FIRST ANGLE PROJECTION

UNIT : mm
Tolerance : ± 0.2